


CF 500/COV AI TWIN - Covering hood



1212266

<https://www.phoenixcontact.com/us/products/1212266>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hood for CF 500 automatic crimping device, for TWIN ferrules: 4 mm² ... 10 mm²
(AI-TWIN 10)

Commercial data

Item number	1212266
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356450188
Weight per piece (including packing)	42.5 g
Weight per piece (excluding packing)	43.2 g
Customs tariff number	84799070
Country of origin	DE

CF 500/COV AI TWIN - Covering hood



1212266

<https://www.phoenixcontact.com/us/products/1212266>

Technical data

Product properties

Product type	Cover
--------------	-------

Connection data

Conductor cross-section flexible	4 mm ² ... 10 mm ²
----------------------------------	--

Dimensions

Width	22.5 mm
Height	70 mm
Length	105 mm

Material specifications

Color	transparent
Material	Plastic
Material for screw connection	Metal

CF 500/COV AI TWIN - Covering hood



1212266

<https://www.phoenixcontact.com/us/products/1212266>

Classifications

ECLASS

ECLASS-15.0	17130192
ECLASS-13.0	17130192

ETIM

ETIM 10.0	EC002778
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 500/COV AI TWIN - Covering hood



1212266

<https://www.phoenixcontact.com/us/products/1212266>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	6.016 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com