

# CSS 0.25-3/3-EMC - Speed starter



1201713

<https://www.phoenixcontact.com/us/products/1201713>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Speed starter with soft start and configurable speed for starting and reversing motors up to 480 V AC and 0.25 kW, configurable motor protection, analog input, STO function up to SIL 3/PL e, three-phase load input, with integrated EMC filter

## Commercial data

Item number	1201713
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C473
Product key	DK7321
GTIN	4063151265786
Weight per piece (including packing)	1,240 g
Weight per piece (excluding packing)	1,240 g
Customs tariff number	85371098
Country of origin	CN

1201713

<https://www.phoenixcontact.com/us/products/1201713>

## Technical data

### Product properties

Product type	Speed starter
Product family	CONTACTRON
Operating elements	Push button
	Rotary switch

### Insulation characteristics

Pollution degree	2
------------------	---

### Electrical properties

Number of phases	3
------------------	---

### Input data

#### Mains

Number of phases	3
Input voltage	380 V AC
	400 V AC
	480 V AC
Input voltage range	220 V AC ... 480 V AC -15 % ... +10 %
Frequency range	47 Hz ... 63 Hz
Nominal current	1 A (no line reactor)
	0.9 A (with line reactor)

### Output data

Nominal motor power	0.25 kW
Apparent power	0.6 kVA
Nominal output current ( $I_N$ )	0.9 A (4 kHz)
	0.6 A (8 kHz)
	0.4 A (16 kHz)
Output frequency	0 Hz ... 500 Hz
Power dissipation	16 W (2 kHz)
	20 W (4 kHz)
	19 W (8 kHz)
	19 W (16 kHz)
	9 W (stand by)
Output current	≤ 1.35 A (180 s)
	≤ 0.675 A (180 s, during recovery time)
	≤ 1.62 A (15 s)
	≤ 0.45 A (15 s, during recovery time)
Recovery time	150 s (180 s)
	12 s (15 s)

# CSS 0.25-3/3-EMC - Speed starter



1201713

<https://www.phoenixcontact.com/us/products/1201713>

Overload time	30 s (180 s)
	3 s (15 s)
Discharge time	3 min (Intermediate circuit capacitors)

## Switching

Output name	Relay output
Contact switching type	1 changeover contact
Maximum switching voltage	125 V AC
	30 V DC
Maximum inrush current	3 A
Inrush current, minimum	10 mA (5 V DC)

## Connection data

### Power-level terminals

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup> (with ferrule)
Conductor cross-section AWG	24 ... 10

### Control terminals

Connection method	Push-in connection
Stripping length	10 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (with ferrule)
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	0.2 mm <sup>2</sup> ... 0.75 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Dimensions

### Drill hole

Diameter	5.5 mm
Width	35 mm
Height	210 mm
Depth	195 mm
Length	≤ 30 m (Motor cable length (EMC compliance category C3))
	≤ 50 m (Motor cable length (no EMC compliance))

## Material specifications

Color	gray (RAL 7042)
-------	-----------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (IP)	IP20
---------------------------	------

# CSS 0.25-3/3-EMC - Speed starter



1201713

<https://www.phoenixcontact.com/us/products/1201713>

Degree of protection (NEMA)	NEMA 1
Ambient temperature (operation)	-20 °C ... 55 °C (without current derating) -20 °C ... 60 °C (with linear current derating)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Altitude	≤ 2000 m > 2000 m (with derating)
Permissible humidity (operation)	90 % (non-condensing)
Permissible humidity (storage/transport)	95 % (non-condensing)
Shock (operation)	15g, 11 ms
Vibration (operation)	0.075 mm/1g
Air pressure (operation)	86 kPa ... 106 kPa
Air pressure (storage/transport)	70 kPa ... 106 kPa

## Approvals

### Safety Integrity Level (SIL, IEC 61800-5-2)

Identification	3
----------------	---

### Performance Level (EN ISO 13849)

Identification	e
----------------	---

### Category (ISO 13849)

Identification	4
----------------	---

## Standards and regulations

Standards/regulations	IEC 61800-5-1 IEC 61800-3
-----------------------	------------------------------

## Mounting

Mounting type	DIN rail mounting Panel mounting
---------------	-------------------------------------

# CSS 0.25-3/3-EMC - Speed starter



1201713

<https://www.phoenixcontact.com/us/products/1201713>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1201713>



### UL Listed

Approval ID: FILE E 322526



### cUL Listed

Approval ID: FILE E 322526



### Functional Safety

Approval ID: 01/205/5866.01/23



### Functional Safety

Approval ID: 01/205/5866.01/23



### Functional Safety

Approval ID: Reg01/205/5866.01/23



### Functional Safety

Approval ID: Reg01/205/5866.01/23



### Functional Safety

Approval ID: 968/FSP 1144.04/23



### cULus Listed

Approval ID: E322526V1S1

# CSS 0.25-3/3-EMC - Speed starter



1201713

<https://www.phoenixcontact.com/us/products/1201713>

## Classifications

### ECLASS

ECLASS-13.0	27142320
ECLASS-15.0	27142320
ECLASS-15.0 ASSET	27250101

### ETIM

ETIM 10.0	EC000256
-----------	----------

### UNSPSC

UNSPSC 21.0	26111500
-------------	----------

# CSS 0.25-3/3-EMC - Speed starter



1201713

<https://www.phoenixcontact.com/us/products/1201713>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
	Bis(2-(2-methoxyethoxy)ethyl)ether(CAS: 143-24-8)
SCIP	5012de76-0fcd-4dfc-8a0d-80045e5e10b3

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)