

CRIMPFOX-M CX-12/DIE - Crimp insert

1212753

<https://www.phoenixcontact.com/us/products/1212753>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die, for CRIMPFOX-M, for coaxial connectors

Your advantages

- Die for CRIMPFOX universal pliers

Commercial data

Item number	1212753
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BH313Z
GTIN	4046356858120
Weight per piece (including packing)	78.5 g
Weight per piece (excluding packing)	78.5 g
Country of origin	SE

CRIMPFOX-M CX-12/DIE - Crimp insert



1212753

<https://www.phoenixcontact.com/us/products/1212753>

Technical data

Product properties

Product type	Die
Compression	HEX crimp
Product property	Replacement insert for CRIMPFOX-M universal crimping pliers
Crimping width	1.46 mm
Crimping width	5.18 mm
Crimping width	6.81 mm

Material specifications

Color	black
-------	-------

CRIMPFOX-M CX-12/DIE - Crimp insert



1212753

<https://www.phoenixcontact.com/us/products/1212753>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212753>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-M CX-12/DIE - Crimp insert



1212753

<https://www.phoenixcontact.com/us/products/1212753>

Classifications

ECLASS

ECLASS-13.0

21043892

ETIM

ETIM 9.0

EC001282

UNSPSC

UNSPSC 21.0

27111500

CRIMPFOX-M CX-12/DIE - Crimp insert



1212753

<https://www.phoenixcontact.com/us/products/1212753>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com