

# ZAP 100 - Crimping tool, pneumatic



1203259

<https://www.phoenixcontact.com/us/products/1203259>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pneumatic crimping pliers, for ferrules in accordance with DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross-section 4 - 10 mm<sup>2</sup>

## Your advantages

- These crimping pliers are pneumatic tools for ferrules with a cross section range of 0.25 mm<sup>2</sup> ... 10 mm<sup>2</sup>

## Commercial data

Item number	1203259
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3232
GTIN	4017918018146
Weight per piece (including packing)	754.9 g
Weight per piece (excluding packing)	711.8 g
Customs tariff number	84671900
Country of origin	DE

# ZAP 100 - Crimping tool, pneumatic



1203259

<https://www.phoenixcontact.com/us/products/1203259>

## Technical data

### Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Air consumption per compression	0.2 l
Pressure range	4.00 bar ... 6.00 bar
Product property	Start the crimping cycle using the manual switch
	Eye for using a balancer
	Several die nests
	Die width: 12 mm
	Insertion funnel allows for easy positioning

### Electrical properties

Frequency range	0 Hz
-----------------	------

### Connection data

#### Conductor connection

Cross section range, metric	4 mm <sup>2</sup> ... 10 mm <sup>2</sup>
-----------------------------	--

### Dimensions

Width	44 mm
Height	44 mm
Length	200 mm

# ZAP 100 - Crimping tool, pneumatic



1203259

<https://www.phoenixcontact.com/us/products/1203259>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1203259>



**EAC**

Approval ID: RU C-DE.AI30.B.01549



**EAC**

Approval ID: 0278662

# ZAP 100 - Crimping tool, pneumatic

1203259

<https://www.phoenixcontact.com/us/products/1203259>



## Classifications

### ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

### ETIM

ETIM 10.0	EC002778
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# ZAP 100 - Crimping tool, pneumatic



1203259

<https://www.phoenixcontact.com/us/products/1203259>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	67.21 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)