

PV-PRO/M/F-200/F-1500/17 - Fuse plug



1220809

<https://www.phoenixcontact.com/us/products/1220809>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse plug, Range of articles: SUNCLIX, color: black, rated voltage: 1500 V DC (bis 4000m ü. NN), rated current: 17 A, Connection method: SUNCLIX PV connector, SUNCLIX fuse element for protecting panels and devices in photovoltaic systems

Commercial data

Item number	1220809
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	AB02
Product key	ABLBEA
GTIN	4063151305789
Weight per piece (including packing)	141.25 g
Weight per piece (excluding packing)	145.262 g
Customs tariff number	85354000
Country of origin	PL

PV-PRO/M/F-200/F-1500/17 - Fuse plug



1220809

<https://www.phoenixcontact.com/us/products/1220809>

Technical data

Notes

General	SUNCLIX fuse element for protecting panels and devices in photovoltaic systems
---------	--

Product properties

Product type	Fuse
Product family	SUNCLIX

Insulation characteristics

Protection class	II
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	1500 V
Rated voltage	1500 V DC (bis 4000m ü. NN)
Rated surge voltage	16 kV
Fuse adapter nominal current	17 A DC (Nominal current of the item)
Fuse-link nominal current	20 A DC (Nominal current of the fuse-link)

Connection data

Connection method	SUNCLIX PV connector
-------------------	----------------------

Material specifications

Color	black
Flammability rating according to UL 94	V0

Cable/line

Cable type	H1Z2Z2-K
------------	----------

Mechanical properties

Mechanical data

Insertion force	45 N ±10 N
Withdrawal force	250 N ±100 N

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 50 °C (Deviating ambient temperatures possible depending on the current carrying capacity/derating curve)
Ambient temperature (assembly)	-25 °C ... 50 °C

Standards and regulations

PV-PRO/M/F-200/F-1500/17 - Fuse plug



1220809

<https://www.phoenixcontact.com/us/products/1220809>

Standards/specifications	2 PfG 2380-2014-02
Note	in progress

PV-PRO/M/F-200/F-1500/17 - Fuse plug



1220809

<https://www.phoenixcontact.com/us/products/1220809>

Classifications

ECLASS

ECLASS-13.0

27440190

ETIM

ETIM 9.0

EC002943

UNSPSC

UNSPSC 21.0

39121400

PV-PRO/M/F-200/F-1500/17 - Fuse plug



1220809

<https://www.phoenixcontact.com/us/products/1220809>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com