

PTFIX 12X2,5 GY-EX - Distribution block



1221410
<https://www.phoenixcontact.com/us/products/1221410>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distribution block, Ex e-certified basic terminal block, mounting type: for snapping onto a DIN rail adapter, Direct mounting with flange, Free-hanging, color: gray

Your advantages

- Ex e certified
- Flexible use, thanks to DIN rail mounting, direct mounting or adhesive mounting
- Clear wiring, thanks to eleven different color variants
- Time-saving conductor connection, thanks to tool-free Push-in direct connection technology
- Time savings of up to 80 %, thanks to ready-to-mount blocks without manual bridging
- Space savings of up to 50 % on the DIN rail, thanks to transverse mounting

Commercial data

Item number	1221410
Packing unit	8 pc
Minimum order quantity	8 pc
Sales key	BE09
Product key	BEA114
GTIN	4063151309336
Weight per piece (including packing)	22.5 g
Weight per piece (excluding packing)	22.5 g
Customs tariff number	85369010
Country of origin	PL

PTFIX 12X2,5 GY-EX - Distribution block



1221410

<https://www.phoenixcontact.com/us/products/1221410>

Technical data

Notes

Notes on operation	the blocks can be bridged with one another via the conductor shaft, for corresponding plug-in bridges, see accessories
--------------------	--

Product properties

Product type	Distributor terminal block
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W

Connection data

Stripping length	8 mm ... 10 mm
------------------	----------------

Ex data

Rated data (ATEX/IECEx)

Identification	Ex II 2 G Ex eb IIC Gb
Operating temperature range	-60 °C ... 110 °C
Ex-certified accessories	3274054 PTFIX-NS35
	3274056 PTFIX-NS35A
	3274057 PTFIX-NS35A-FIX
	3274058 PTFIX-NS15A
	3274059 PTFIX-NS15A-FIX
	3274060 PTFIX-F
	3022263 CLIPFIX 15
	3022276 CLIPFIX 35-5
	3022218 CLIPFIX 35
1204517 SZF 1-0,6X3,5	
List of bridges	Plug-in bridge / FBS 2-5 / 3030161
Bridge data	23 A (2.5 mm²)
Ex temperature increase	40 K (22.5 A / 2.5 mm²)
Rated insulation voltage when mounting on DIN rails	400 V
Rated insulation voltage when directly mounted on mounting surface	400 V
output	(Permanent)

Ex level General

PTFIX 12X2,5 GY-EX - Distribution block



1221410

<https://www.phoenixcontact.com/us/products/1221410>

Rated voltage when mounting on DIN rails	440 V
Rated voltage during direct mounting on mounting surface	440 V
Rated current	22.5 A (2.5 mm ²)
Maximum load current	27 A (4 mm ²)
Contact resistance	0.6 mΩ

Ex connection data General

Nominal cross section	2.5 mm ²
Rated cross section AWG	14
Connection capacity rigid	0.14 mm ² ... 4 mm ²
Connection capacity AWG	26 ... 12
Connection capacity flexible	0.14 mm ² ... 2.5 mm ²
Connection capacity AWG	26 ... 14

Dimensions

Width	31.5 mm
Height	28.6 mm
Depth	21.7 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	for snapping onto a DIN rail adapter
	Direct mounting with flange
	Free-hanging

PTFIX 12X2,5 GY-EX - Distribution block


1221410

<https://www.phoenixcontact.com/us/products/1221410>



Drawings

Circuit diagram



PTFIX 12X2,5 GY-EX - Distribution block



1221410

<https://www.phoenixcontact.com/us/products/1221410>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1221410>



IECEx

Approval ID: IECExSEV21.0023U



ATEX

Approval ID: SEV21ATEX0557U



UKCA-EX

Approval ID: CML 22UKEX3672U



CCC

Approval ID: 2026322303007145

PTFIX 12X2,5 GY-EX - Distribution block



1221410

<https://www.phoenixcontact.com/us/products/1221410>

Classifications

ECLASS

ECLASS-13.0	27250118
ECLASS-15.0	27250118

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTFIX 12X2,5 GY-EX - Distribution block



1221410

<https://www.phoenixcontact.com/us/products/1221410>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com