

FOC-ADAPTER:SCD/SCD-MM-ME - FO coupling



1208083

<https://www.phoenixcontact.com/us/products/1208083>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

FO coupling, degree of protection: IP20, number of positions: 2, material: Metal, connection method: Coupling, cable outlet: straight, color: silver/matt, Ethernet



Your advantages

- High reliability with comprehensive quality assurance measures
- Optimized precision (stability) with the use of ceramic sleeves
- Versatile range of applications with an extended temperature range and various mounting options
- Suitable for use for all multimode classes
- Optimum compatibility with the FDX20 series splice boxes
- Future-proof, thanks to RoHS 2 conformity

Commercial data

Item number	1208083
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	AB16
Product key	ABNIDA
GTIN	4063151276591
Weight per piece (including packing)	20.666 g
Weight per piece (excluding packing)	18.8 g
Customs tariff number	85367000
Country of origin	CN

1208083

<https://www.phoenixcontact.com/us/products/1208083>

Technical data

Product properties

Product type	Data plug
Type	SC
Number of positions	2
Connection profile	SC
Number of slots	2
Cable outlet	straight

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated surge voltage	0.8 kV
Attenuation	≤ 0.2 dB
Insulation resistance	≥ 500 MΩ
Nominal current I_N	0.5 A
Transmission medium	FO

Connection data

Connection method	Coupling
-------------------	----------

Interfaces

Signal type/category	Ethernet
----------------------	----------

Dimensions

Width	34.7 mm
Height	9.4 mm
Length	27.4 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Color	silver/matt
Color of the housing part	silver
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact surface material	Gold

Cable/line

Cable type	Fiberglass
------------	------------

FOC-ADAPTER:SCD/SCD-MM-ME - FO coupling



1208083

<https://www.phoenixcontact.com/us/products/1208083>

Signal type/category	Ethernet
External sheath, color	silver-colored
Tensile strength short-term/long-term	40 N
Halogen-free	yes
Resistance to oil	yes
Flame resistance	yes

FO cable

Number of fibers	2
Fiber	50/125 µm
Fiber type	Fiberglass
Attenuation	≤ 0.15 dB

Mechanical properties

Tensile strength short-term/long-term	40 N
---------------------------------------	------

Characteristics

Attenuation	≤ 0.2 dB
-------------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-55 °C ... 85 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to UV radiation	yes
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes

1208083

<https://www.phoenixcontact.com/us/products/1208083>

Classifications

ECLASS

ECLASS-13.0	19170116
ECLASS-15.0	19170116

ETIM

ETIM 10.0	EC000752
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FOC-ADAPTER:SCD/SCD-MM-ME - FO coupling



1208083

<https://www.phoenixcontact.com/us/products/1208083>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com