

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 7.5 m, number of positions: 8, CAT5, connection method: Pierce connection, connection cross section: AWG 26- 26, cable outlet: straight, Ethernet, 2x2xAWG26/7, S/UTP, gray

Your advantages

- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- High-speed data transmission with up to 1 Gbps (CAT5)



Commercial data

Item number	1227565
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB11
Product key	ABNABG
GTIN	4063151322106
Weight per piece (including packing)	363.6 g
Weight per piece (excluding packing)	342 g
Customs tariff number	85444290
Country of origin	CN

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Technical data

Product properties

Product type	Data cable preassembled
Product family	RJ45 STANDARD CAT5
Number of positions	8
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Interfaces

Signal type/category	Ethernet CAT5 (IEC 11801:2002)
----------------------	--------------------------------

Electrical properties

Rated voltage (III/2)	72 V
Transmission medium	Copper
Transmission characteristics (category)	CAT5
Power transmission	PoE++

Mechanical properties

Mechanical data

Insertion force per signal contact	30.00 N
Extraction force per signal contact	50 N

Material specifications

Flammability rating according to UL 94	V0
Contact material	Brass
Contact surface material	Au
Contact carrier material	PC
Outer sheath, material	LSZH

Dimensions

Width	11.6 mm
Height	14.8 mm
Length	40 mm

Connection data

Connection technology

Connection method	Pierce connection
-------------------	-------------------

Conductor connection

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Connection method	Pierce connection
-------------------	-------------------

Connector

Connection 1

Type	Plug straight RJ45
Shielded	yes
Handle color	gray
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

Connection 2

Type	Plug straight RJ45
Shielded	yes
Handle color	gray
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C

Cable/line

Cable length	7.50 m
--------------	--------

Ethernet, Type B, 8-pos., CAT5, LSZH [BC5]

Number of positions	8
Shielded	yes
Cable type	Ethernet, Type B, 8-pos., CAT5, LSZH [BC5]
Conductor structure	2x2xAWG26/7, S/UTP
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Wire diameter incl. insulation	0.85 mm
External cable diameter	5.70 mm ±0.3 mm
Outer sheath, material	LSZH
External sheath, color	gray
Conductor material	Bare Cu litz wires
Material wire insulation	PE
Single wires, quantity	8
Single wire, cross section [AWG]	26
Thickness, outer sheath	approx. 0.70 mm
Optical shield covering	70 %
Insulation resistance	≥ 5000 MΩ*km
Loop resistance	≤ 148.00 Ω/km
Wave impedance	100 Ω
Minimum bending radius, fixed installation	8 x D
Smallest bending radius, fixed installation	46 mm
	65.3 dB (with 1 MHz)

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Near end crosstalk attenuation (NEXT)	56.3 dB (at 4 MHz)
	50.3 dB (at 10 MHz)
	47.2 dB (at 16 MHz)
	45.8 dB (at 20 MHz)
	42.9 dB (at 31.25 MHz)
	38.4 dB (at 62.5 MHz)
	35.3 dB (at 100 MHz)
Power-summated near end crosstalk attenuation (PSNEXT)	62.3 dB (with 1 MHz)
	53.3 dB (at 4 MHz)
	48.8 dB (at 8 MHz)
	47.3 dB (at 10 MHz)
	44.2 dB (at 16 MHz)
	42.8 dB (at 20 MHz)
	41.3 dB (at 25 MHz)
	39.9 dB (at 31.25 MHz)
	35.4 dB (at 62.5 MHz)
	32.3 dB (at 100 MHz)
Return attenuation (RL)	20 dB (with 1 MHz)
	23 dB (at 4 MHz)
	24.5 dB (at 8 MHz)
	25 dB (at 10 MHz)
	25 dB (at 16 MHz)
	25 dB (at 20 MHz)
	24.2 dB (at 25 MHz)
	23.3 dB (at 31.25 MHz)
	20.7 dB (at 62.5 MHz)
19 dB (at 100 MHz)	
Shield attenuation	3.2 dB (with 1 MHz)
	6.01 dB (at 4 MHz)
	9.49 dB (at 10 MHz)
	12.07 dB (at 16 MHz)
	13.54 dB (at 20 MHz)
	17.11 dB (at 31.25 MHz)
	24.76 dB (at 62.5 MHz)
	31.99 dB (at 100 MHz)
Halogen-free	complying with IEC 60754-1/2
Flame resistance	IEC 60332-1-2/IEC 60332-3-24/CM
Ambient temperature (operation)	-20 °C ... 80 °C (cable, fixed installation)
	-20 °C ... 80 °C (Cable, flexible installation)
Ambient temperature (installation)	0 °C ... 60 °C

Environmental and real-life conditions

Ambient conditions

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C

Standards and regulations

Flame resistance	IEC 60332-1-2
------------------	---------------

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1227565>



EAC

Approval ID: 19060508



UL Listed

Approval ID: E335024_20210804



cUL Listed

Approval ID: E335024_20210804

NBC-R40C/7,5-BC5/R40C - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

NBC-R4OC/7,5-BC5/R4OC - Patch cable



1227565

<https://www.phoenixcontact.com/us/products/1227565>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	12.193 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com