

# CF 1000-1,5 120V - Tool



1208209

<https://www.phoenixcontact.com/us/products/1208209>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Automatic stripping and crimping device, 120 V version, for insulated ferrules with a cross-section range from 0.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, according to DIN 46228-4: 1990-09

## Your advantages

- Quantity counter
- The conductor is stripped in a single step and crimped with a ferrule to a high standard of quality
- The pull-out forces meet the requirements of IEC/EN 60999 and IEC/EN 60947
- The automatic stripping and crimping device can be used to process loose ferrules with insulating collars according to DIN 46228-4
- Quick change of cross section without the need for additional adjustments
- Suitable for bulk processing
- Rugged design

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1208209                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | NULL                           |
| Product key                          | BH3232                         |
| GTIN                                 | 4046356011358                  |
| Weight per piece (including packing) | 99 g                           |
| Weight per piece (excluding packing) | 99 g                           |
| Customs tariff number                | 84798100                       |
| Country of origin                    | DE                             |

# CF 1000-1,5 120V - Tool

1208209

<https://www.phoenixcontact.com/us/products/1208209>



## Technical data

### Product properties

|                                 |             |
|---------------------------------|-------------|
| Compression                     | trapezoidal |
| Air consumption per compression | 1.2 l       |

### Electrical properties

#### Supply

|                |       |
|----------------|-------|
| Supply voltage | 120 V |
|----------------|-------|

### Connection data

|                                  |  |
|----------------------------------|--|
| Conductor cross-section flexible | 0.34 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
|----------------------------------|--|

### Dimensions

|        |        |
|--------|--------|
| Width  | 240 mm |
| Height | 390 mm |
| Length | 490 mm |

### Standards and regulations

|       |                      |
|-------|----------------------|
| Tests | DIN 46228-4: 1990-09 |
|-------|----------------------|

# CF 1000-1,5 120V - Tool

1208209

<https://www.phoenixcontact.com/us/products/1208209>



## Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)