NS 35/15 PERF 2M NZ REF CUT - DIN rail

1210240

https://www.phoenixcontact.com/us/products/1210240

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, similar to EN 60715, material: Steel, zinc plating, color: silver

Commercial data


Item number	1210240
Packing unit	5 pc
Minimum order quantity	10 pc
Sales key	BE72
Product key	BH8422
GTIN	4046356528573
Weight per piece (including packing)	1.26 g
Weight per piece (excluding packing)	1.26 g
Customs tariff number	72166190
Country of origin	DE

Technical data

Product properties

Product type	DIN rail

Dimensions

Dimensional drawing	
Width	35 mm
Hole width	15 mm
Hole height	6.2 mm
Depth	15 mm
Length	2000 mm
Drill hole spacing	25 mm

Material specifications

Color	silver
Material	Steel
Coating	zinc plating

Standards and regulations

Tests	similar to EN 60715


Electrical tests

Short-time withstand current

Max. permissible thermal nominal current for PEN function	232 A

Drawings

Dimensional drawing



Classifications

ECLASS

ECLASS-13.0	27400602
ECLASS-15.0	27400602

ETIM

ETIM 10.0	EC001285

UNSPSC

UNSPSC 21.0	39121700

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	2.695 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com