

# CRIMPFOX 6 - Crimping pliers



1212034

<https://www.phoenixcontact.com/us/products/1212034>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm<sup>2</sup> ... 6.0 mm<sup>2</sup>, lateral entry, trapezoidal crimp

## Your advantages

- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Unlockable pressure lock
- Comprehensive range of crimping pliers
- Consistently high crimping quality
- Marked die stations for precise processing of corresponding cross sections

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1212034       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH3131        |
| GTIN                                 | 4046356453813 |
| Weight per piece (including packing) | 444.2 g       |
| Weight per piece (excluding packing) | 444.2 g       |
| Customs tariff number                | 82032000      |
| Country of origin                    | SE            |

# CRIMPFOX 6 - Crimping pliers



1212034

<https://www.phoenixcontact.com/us/products/1212034>

## Technical data

### Notes

#### Environmental Product Compliance

|                           |   |
|---------------------------|---|
| California Proposition 65 | Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration |
|---------------------------|---|

### Product properties

|                  |                                    |
|------------------|------------------------------------|
| Product type     | Crimping tool                      |
| Compression      | Trapezoidal crimp                  |
| Product property | Compact design                     |
|                  | Low grip span                      |
|                  | Ergonomic two-component handle     |
|                  | Tool-free unlockable pressure lock |
|                  | Crimping force can be readjusted   |

#### Crimping position 1

|                    |                      |
|--------------------|----------------------|
| Min. cross section | 0.25 mm <sup>2</sup> |
| Max. cross section | 0.75 mm <sup>2</sup> |
| AWG min            | 24                   |
| AWG max            | 20                   |

#### Crimping position 2

|                    |                     |
|--------------------|---------------------|
| Min. cross section | 1 mm <sup>2</sup>   |
| Max. cross section | 1.5 mm <sup>2</sup> |
| AWG min            | 18                  |
| AWG max            | 16                  |

#### Crimping position 3

|                    |                     |
|--------------------|---------------------|
| Max. cross section | 2.5 mm <sup>2</sup> |
| AWG max            | 14                  |

#### Crimping position 4

|                    |                   |
|--------------------|-------------------|
| Max. cross section | 4 mm <sup>2</sup> |
| AWG max            | 12                |

#### Crimping position 5

|                    |                   |
|--------------------|-------------------|
| Max. cross section | 6 mm <sup>2</sup> |
| AWG max            | 10                |

### Connection data

#### Conductor connection

|                             |  |
|-----------------------------|--|
| Cross section range, metric | 0.25 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Cross section range AWG     | 24 ... 10                                  |

# CRIMPFOX 6 - Crimping pliers



1212034

<https://www.phoenixcontact.com/us/products/1212034>

## Dimensions

|        |        |
|--------|--------|
| Width  | 18 mm  |
| Height | 59 mm  |
| Length | 198 mm |

## Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX 6 - Crimping pliers


1212034

<https://www.phoenixcontact.com/us/products/1212034>



## Drawings

Product drawing



# CRIMPFOX 6 - Crimping pliers



1212034

<https://www.phoenixcontact.com/us/products/1212034>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212034>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 6 - Crimping pliers



1212034

<https://www.phoenixcontact.com/us/products/1212034>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043811 |
| ECLASS-15.0 | 21043811 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000168 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX 6 - Crimping pliers



1212034

<https://www.phoenixcontact.com/us/products/1212034>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)