

# CRIMPFOX-M TC 4/DIE - Crimp insert

1212075

<https://www.phoenixcontact.com/us/products/1212075>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Die, for Crimpfox-M, for turned contacts 0.5 ... 4 mm<sup>2</sup>, packed in a serial storage box



## Your advantages

- For CK 2,5 ED..., CK 4,0 ED... turned pin and socket contacts
- Marked die stations for precise processing of corresponding cross sections

## Commercial data

Item number	1212075
Packing unit	1 pc
Sales key	BH31
Product key	BH313Y
GTIN	4046356452540
Weight per piece (including packing)	79.25 g
Weight per piece (excluding packing)	73.3 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-M TC 4/DIE - Crimp insert



1212075

<https://www.phoenixcontact.com/us/products/1212075>

## Technical data

### Product properties

Product type	Die
Compression	Square crimp
Product property	For CK 2,5 ED... and CK 4,0 ED... turned male and female contacts
	Marked die stations
	Replacement insert for CRIMPFOX-M universal crimping pliers

### Crimping position 1

Min. cross section	0.5 mm <sup>2</sup>
Max. cross section	1 mm <sup>2</sup>
AWG min	20
AWG max	18

### Crimping position 2

Max. cross section	1.5 mm <sup>2</sup>
AWG max	16

### Crimping position 3

Max. cross section	2.5 mm <sup>2</sup>
AWG max	14

### Crimping position 4

Max. cross section	4 mm <sup>2</sup>
AWG max	12

### Connection data

#### Conductor connection

Cross section range, metric	0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Cross section range AWG	20 ... 12

### Dimensions

Width	75 mm
Height	25.5 mm
Length	114 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX-M TC 4/DIE - Crimp insert



1212075

<https://www.phoenixcontact.com/us/products/1212075>

## Classifications

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-M TC 4/DIE - Crimp insert



1212075

<https://www.phoenixcontact.com/us/products/1212075>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)