

CRIMPFOX-M RC 2,5/DIE - Crimp insert



1212078

<https://www.phoenixcontact.com/us/products/1212078>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Die, for Crimpfox-M, for non-insulated cable lugs 0.75 - 2.5 mm², packed in a serial storage box



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212078 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BH31 |
| Product key | BH313Z |
| GTIN | 4046356454476 |
| Weight per piece (including packing) | 79.03 g |
| Weight per piece (excluding packing) | 75.1 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX-M RC 2,5/DIE - Crimp insert



1212078

<https://www.phoenixcontact.com/us/products/1212078>

Technical data

Product properties

| | |
|------------------|---|
| Product type | Die |
| Compression | Indent crimp |
| Product property | Replacement insert for CRIMPFOX-M universal crimping pliers |

Crimping position 1

| | |
|--------------------|----------------------|
| Max. cross section | 0.75 mm ² |
| AWG max | 20 |

Crimping position 2

| | |
|--------------------|---------------------|
| Max. cross section | 1.5 mm ² |
| AWG max | 16 |

Crimping position 3

| | |
|--------------------|---------------------|
| Max. cross section | 2.5 mm ² |
| AWG max | 14 |

Connection data

Conductor connection

| | |
|-----------------------------|--|
| Cross section range, metric | 0.75 mm ² ... 2.5 mm ² |
|-----------------------------|--|

Dimensions

| | |
|--------|---------|
| Width | 75 mm |
| Height | 25.5 mm |
| Length | 114 mm |

Material specifications

| | |
|-------|-------|
| Color | black |
|-------|-------|

CRIMPFOX-M RC 2,5/DIE - Crimp insert



1212078

<https://www.phoenixcontact.com/us/products/1212078>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212078>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-M RC 2,5/DIE - Crimp insert



1212078

<https://www.phoenixcontact.com/us/products/1212078>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 21043892 |
| ECLASS-15.0 | 21043892 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC011822 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-M RC 2,5/DIE - Crimp insert



1212078

<https://www.phoenixcontact.com/us/products/1212078>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com