

# CRIMPFOX-DSUB 5 - Crimping pliers



1212111

<https://www.phoenixcontact.com/us/products/1212111>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers for D-SUB contacts, high-density, 0.08 - 0.5 mm<sup>2</sup>, B-crimp, including contact locator

## Your advantages

- Lateral conductor entry
- Unlockable pressure lock
- High crimping force with low manual force
- Marked die stations for precise processing of corresponding cross sections

## Commercial data

Item number	1212111
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3136
GTIN	4046356453899
Weight per piece (including packing)	445.3 g
Weight per piece (excluding packing)	442.9 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-DSUB 5 - Crimping pliers



1212111

<https://www.phoenixcontact.com/us/products/1212111>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	B crimp
Product property	Lateral conductor entry
	Unlockable pressure lock
	Marked die stations

#### Crimping position 1

Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	0.22 mm <sup>2</sup>
AWG min	28
AWG max	26

#### Crimping position 2

Min. cross section	0.08 mm <sup>2</sup>
Max. cross section	0.22 mm <sup>2</sup>
AWG min	28
AWG max	26

#### Crimping position 3

Min. cross section	0.22 mm <sup>2</sup>
Max. cross section	0.5 mm <sup>2</sup>
AWG min	26
AWG max	22

### Connection data

#### Conductor connection

Cross section range, metric	0.08 mm <sup>2</sup> ... 0.5 mm <sup>2</sup>
Cross section range AWG	28 ... 22

### Dimensions

Width	18 mm
Height	59 mm
Length	198 mm

### Material specifications

Color	black
-------	-------


# CRIMPFOX-DSUB 5 - Crimping pliers

1212111

<https://www.phoenixcontact.com/us/products/1212111>

## Drawings

### Product drawing



# CRIMPFOX-DSUB 5 - Crimping pliers



1212111

<https://www.phoenixcontact.com/us/products/1212111>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212111>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-DSUB 5 - Crimping pliers



1212111

<https://www.phoenixcontact.com/us/products/1212111>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-DSUB 5 - Crimping pliers



1212111

<https://www.phoenixcontact.com/us/products/1212111>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)