

CRIMPFOX-TC 10 - Crimping pliers



1212114

<https://www.phoenixcontact.com/us/products/1212114>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for turned contacts with a pin diameter of 4.0 mm, two marked die stations, pressure lock can be released, lateral entry, incl. positioning help

Your advantages

- Crimping pliers for processing turned contacts
- The integrated positioning tool ensures that the contacts are perfectly aligned in the die
- Marked die stations for precise processing of corresponding cross sections

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1212114 |
| Packing unit | 1 pc |
| Sales key | BH31 |
| Product key | BH3135 |
| GTIN | 4046356454025 |
| Weight per piece (including packing) | 724.5 g |
| Weight per piece (excluding packing) | 724.5 g |
| Customs tariff number | 82032000 |
| Country of origin | SE |

CRIMPFOX-TC 10 - Crimping pliers



1212114

<https://www.phoenixcontact.com/us/products/1212114>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Crimping tool

Compression

Square crimp

Crimping position 1

Max. cross section

6 mm²

AWG max

10

Crimping position 2

Max. cross section

10 mm²

AWG max

8

Connection data

Conductor connection

Cross section range, metric

6 mm² ... 10 mm²

Cross section range AWG

10 ... 8

Dimensions

Width

25 mm

Height

68 mm

Length

256 mm

Material specifications

Color

black

Material

Steel

CRIMPFOX-TC 10 - Crimping pliers



1212114

<https://www.phoenixcontact.com/us/products/1212114>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

CRIMPFOX-TC 10 - Crimping pliers



1212114

<https://www.phoenixcontact.com/us/products/1212114>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com