

ZAP 40 - Crimping tool, pneumatic



1212630

<https://www.phoenixcontact.com/us/products/1212630>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pneumatic crimping pliers, for ferrules according to DIN 46228-1: 1992-08 and DIN 46228-4: 1990-09, for conductor cross-section 0.25 - 4 mm², trapezoid crimping, lateral entry

Commercial data

Item number	1212630
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH3232
GTIN	4046356661027
Weight per piece (including packing)	778.8 g
Weight per piece (excluding packing)	734.2 g
Customs tariff number	84671900
Country of origin	DE

ZAP 40 - Crimping tool, pneumatic



1212630

<https://www.phoenixcontact.com/us/products/1212630>

Technical data

Product properties

Product type	Automatic crimping device
Compression	trapezoidal
Air consumption per compression	0.2 l
Pressure range	4.00 bar ... 6.00 bar
Product property	Start the crimping cycle using the manual switch
	Eye for using a balancer
	Several die nests
	Die width: 12 mm
	Insertion funnel allows for easy positioning

Electrical properties

Frequency range	0 Hz
Power consumption	0 W

Connection data

Conductor connection

Cross section range, metric	0.25 mm ² ... 4 mm ²
-----------------------------	--

Dimensions

Width	44 mm
Height	44 mm
Length	200 mm

ZAP 40 - Crimping tool, pneumatic



1212630

<https://www.phoenixcontact.com/us/products/1212630>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212630>



EAC

Approval ID: RU C-DE.AI30.B.01549



EAC

Approval ID: 0278662

ZAP 40 - Crimping tool, pneumatic



1212630

<https://www.phoenixcontact.com/us/products/1212630>

Classifications

ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

ETIM

ETIM 10.0	EC002778
-----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

ZAP 40 - Crimping tool, pneumatic



1212630

<https://www.phoenixcontact.com/us/products/1212630>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	93.442 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com