

# CRIMPFOX-RC 6 - Crimping pliers



1212710

<https://www.phoenixcontact.com/us/products/1212710>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Crimping pliers, for uninsulated cable lugs, 0.34 mm<sup>2</sup> ... 6 mm<sup>2</sup>, indent crimp



## Your advantages

- Unlockable pressure lock
- Lateral conductor entry
- Consistently high crimping quality
- Compact and lightweight design
- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working
- Marked die stations for precise processing of corresponding cross sections
- Crimping pliers for uninsulated cable lugs

## Commercial data

Item number	1212710
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3133
GTIN	4046356857598
Weight per piece (including packing)	437.7 g
Weight per piece (excluding packing)	437.7 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX-RC 6 - Crimping pliers



1212710

<https://www.phoenixcontact.com/us/products/1212710>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Indent crimp
Product property	Unlockable pressure lock
	Lateral conductor entry
	Compact and lightweight design
	Marked die stations

#### Crimping position 1

Min. cross section	0.35 mm <sup>2</sup>
Max. cross section	2.5 mm <sup>2</sup>
AWG min	22
AWG max	14

#### Crimping position 2

Min. cross section	4 mm <sup>2</sup>
Max. cross section	6 mm <sup>2</sup>
AWG min	12
AWG max	10

### Connection data

#### Conductor connection

Cross section range, metric	0.34 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Cross section range AWG	22 ... 10

### Dimensions

Width	18 mm
Height	59 mm
Length	198 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX-RC 6 - Crimping pliers



1212710

<https://www.phoenixcontact.com/us/products/1212710>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212710>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-RC 6 - Crimping pliers



1212710

<https://www.phoenixcontact.com/us/products/1212710>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX-RC 6 - Crimping pliers



1212710

<https://www.phoenixcontact.com/us/products/1212710>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements

Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

### EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)