

RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: RC, angled, shielded: no, Screw locking mechanism, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Pin, Solder cup, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1240598
Packing unit	8 pc
Minimum order quantity	1 pc
Product key	ABRAFC
GTIN	4063151422370
Weight per piece (including packing)	154.7 g
Weight per piece (excluding packing)	145.107 g
Country of origin	DE

RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Technical data

Product properties

Product type	Circular connector (cable-side)
Thread type	M23

Material specifications

Flammability rating according to UL 94	V0
--	----

Connection data

Conductor connection

Connection method	Solder connection
-------------------	-------------------

Connector

Insulating body

Coding	N
Material (Insulating body)	PBT
Material (Contact)	CuZn
Material (Contact surface)	Ni/Au
Insertion/withdrawal cycles	50
Connection method	Solder cup
Contact switching type	Pin
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Number (Contact group 1)	1
Contact diameter (Contact group 1)	2 mm
Litz wires Min. cross section (Contact group 1)	0.08 mm ²
Litz wires Max. cross section (Contact group 1)	2.5 mm ²
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Number (Contact group 2)	8
Contact diameter (Contact group 2)	1 mm
Litz wires Max. cross section (Contact group 2)	1 mm ²
Rated current Contact (Contact group 2)	8 A
Rated voltage Contact (Contact group 2)	48 V AC 48 V AC

RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Housing

Type	Cable connector housing
Thread type	M23
Design	angled
Type of locking	Screw locking mechanism
Pg screw connection	Pg9
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP65
	IP67

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
----------------------	------

RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Drawings

Schematic diagram



Connector pin assignment

RC-09P1N12Z500X - Cable connector

1240598

<https://www.phoenixcontact.com/us/products/1240598>

Schematic diagram




Connector pin assignment

RC-09P1N12Z500X - Cable connector

1240598

<https://www.phoenixcontact.com/us/products/1240598>

Schematic diagram



Connector pin assignment


RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Schematic diagram



Dimensional drawing

RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Classifications

ECLASS

ECLASS-13.0

27440116

ETIM

ETIM 9.0

EC003569

RC-09P1N12Z500X - Cable connector



1240598

<https://www.phoenixcontact.com/us/products/1240598>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com