

# CRIMPFOX 10 - Crimping pliers



1212721

<https://www.phoenixcontact.com/us/products/1212721>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 4 mm<sup>2</sup> ... 10 mm<sup>2</sup>, lateral entry, trapezoidal crimp

## Your advantages

- Unlockable pressure lock
- Marked die stations for precise processing of corresponding cross sections
- All ferrules can be optimally crimped with a minimum amount of effort even in the case of large conductor cross-sections
- Consistently high crimping quality

## Commercial data

Item number	1212721
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4046356857802
Weight per piece (including packing)	687.5 g
Weight per piece (excluding packing)	687.5 g
Customs tariff number	82032000
Country of origin	SE

# CRIMPFOX 10 - Crimping pliers



1212721

<https://www.phoenixcontact.com/us/products/1212721>

## Technical data

### Notes

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Product properties

Product type	Crimping tool
Compression	Trapezoidal crimp
Product property	Low actuation force
	Long handle for cross-sections up to 50 mm <sup>2</sup>
	Ergonomic two-component handle
	Tool-free unlockable pressure lock
	Handle with non-slip pad
	Crimping force can be readjusted
	Fastening lug for safety tape

#### Crimping position 1

Max. cross section	4 mm <sup>2</sup>
AWG min	8
AWG max	12

#### Crimping position 2

Max. cross section	6 mm <sup>2</sup>
AWG max	10

#### Crimping position 3

Max. cross section	10 mm <sup>2</sup>
AWG max	8

### Connection data

#### Conductor connection

Cross section range, metric	4 mm <sup>2</sup> ... 10 mm <sup>2</sup>
Cross section range AWG	12 ... 8

### Dimensions

Width	22 mm
Height	80 mm
Length	256 mm

### Material specifications

Color	black
-------	-------

# CRIMPFOX 10 - Crimping pliers



1212721

<https://www.phoenixcontact.com/us/products/1212721>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212721>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX 10 - Crimping pliers



1212721

<https://www.phoenixcontact.com/us/products/1212721>

## Classifications

### ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

### ETIM

ETIM 10.0	EC000168
-----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CRIMPFOX 10 - Crimping pliers



1212721

<https://www.phoenixcontact.com/us/products/1212721>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)