

# TU-07P1N8A8UDUX - Cable connector



1242649

<https://www.phoenixcontact.com/us/products/1242649>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, application: Signal, series: TU, straight, shielded: yes, Bayonet locking, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Pin, Crimp connection, cable diameter range: 2 mm ... 14.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %). This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1242649
Packing unit	12 pc
Minimum order quantity	1 pc
Product key	ABRAHA
GTIN	4063151430719
Weight per piece (including packing)	105.125 g
Weight per piece (excluding packing)	98.723 g
Country of origin	DE

# TU-07P1N8A8UDUX - Cable connector



1242649

<https://www.phoenixcontact.com/us/products/1242649>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Insulating body

Note	Order information: Order crimp contacts Ø 2 mm separately
Coding	N
Material (Insulating body)	PA 6.6
Flammability rating according to UL 94	V0
Connection method	Crimp connection
Contact switching type	Pin
Application	Signal
Number of positions	7
Direction of rotation	Standard
Connection profile	7
Number (Contact group 1)	7
Contact diameter (Contact group 1)	2 mm
Rated current Contact (Contact group 1)	20 A (for max. connection cross section)
Rated voltage Contact (Contact group 1)	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

#### Housing

Type	Cable connector housing
Thread type	M23
Design	straight
Type of locking	Bayonet locking
Pg screw connection	none
Material (Housing)	GD-Zn
Material (Housing surface)	Ni
Material (Rotating parts)	CuZn
Degree of protection (plugged in)	IP67

#### Seal

External cable diameter	2 mm ... 14.5 mm
Seal material	NBR

## Environmental and real-life conditions

#### Ambient conditions

# TU-07P1N8A8UDUX - Cable connector



1242649

<https://www.phoenixcontact.com/us/products/1242649>

Permissible humidity (storage/transport)
--

50 % ... 65 %
---------------

# TU-07P1N8A8UDUX - Cable connector

1242649

<https://www.phoenixcontact.com/us/products/1242649>



## Drawings

Schematic diagram



Connector pin assignment

# TU-07P1N8A8UDUX - Cable connector



1242649

<https://www.phoenixcontact.com/us/products/1242649>

## Classifications

### ECLASS

ECLASS-13.0	27440116
ECLASS-15.0	27440116

### ETIM

ETIM 10.0	EC002635
-----------	----------

# TU-07P1N8A8UDUX - Cable connector



1242649

<https://www.phoenixcontact.com/us/products/1242649>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)