

MICROFOX-P ESD_DB - Needle-nose pliers



1212799

<https://www.phoenixcontact.com/us/products/1212799>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



ESD electronic needle-nose pliers, smooth gripping surface, with opening spring, non-reflective coating and phosphate-treated, 2-component handle, type of packaging: with holder for sales display (backcard)

Figure shows item MICROFOX-P ESD

Product description

Note:
Due to the current challenges of the global procurement market, Phoenix Contact has unfortunately been forced to accept a different ESD-compliant material. In future, the tools will be supplied with plastic handles in black/turquoise. This does not affect the function or quality of the ESD pliers.

Your advantages

- Opening spring for uniform, smooth opening
- Ergonomically designed two-component handles for fatigue-proof and non-slip use
- Through-connected joint for permanent stability and optimum distribution of force
- The special conductive plastic handles ensure slow and safe removal of electrostatic energy according to standards and directives such as DIN EN 61340-5
- Made from special high-grade tool steel
- Mirror-polished and phosphate-treated metal surfaces for optimum rust protection and no glare when working

Commercial data

Item number	1212799
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BH31
Product key	BH3152
GTIN	4046356995078
Weight per piece (including packing)	96.433 g
Weight per piece (excluding packing)	96.433 g
Customs tariff number	82032000
Country of origin	DE

MICROFOX-P ESD_DB - Needle-nose pliers



1212799

<https://www.phoenixcontact.com/us/products/1212799>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type

Electronics pliers

Electrical properties

Fuse

DIN EN 61340-5-1/VDE 0300-5-1, DIN EN 61340-2-3/VDE 0300-2-3

Dimensions

Width

60 mm

Height

7 mm

Length

133 mm

Material specifications

Color

multicolored (RAL -)

Material

Steel

Coating

phosphatized

MICROFOX-P ESD_DB - Needle-nose pliers



1212799

<https://www.phoenixcontact.com/us/products/1212799>

Classifications

ECLASS

ECLASS-13.0	21043816
ECLASS-15.0	21043816

ETIM

ETIM 10.0	EC000835
-----------	----------

UNSPSC

UNSPSC 21.0	27112100
-------------	----------

MICROFOX-P ESD_DB - Needle-nose pliers



1212799

<https://www.phoenixcontact.com/us/products/1212799>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com