THERMOMARK GO SET - Thermal transfer printer set

1221548

https://www.phoenixcontact.com/us/products/1221548

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Mobile thermal transfer printer for marking materials in cartridge format incl. accessories in the practical case from the proven L-BOXX system. The printer can print prepunched labels as well as materials in continuous format up to a material width of 24 mm.

Product description

The THERMOMARK GO SET contains a mobile printer that elevates the digitalization of industrial identification to a new level with its intuitive operation via smart device. Controlled via the MARKING system app, the robust printer creates markings directly on site. Features such as state-of-the-art interfaces, fully guided creation of application-specific identification solutions, and automatic material detection make the process of creating markings particularly easy and error-free. The ability to print die-cut materials as well as continuous media offers professional users a wide variety of applications in industry and trade.

Note:
This product is approved for the following countries only and may only be used in these countries.

Andorra, Armenia, Australia, Austria, Belgium, Brazil, Bulgaria, Canada, Chile, China, Croatia, Cyprus, Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Italy, Japan, Kazakhstan, Kyrgyzstan, Latvia, Liechtenstein, Lithuania, Luxembourg, Malta, Monaco, Morocco, Netherlands, New Zealand, Norway, Poland, Portugal, Romania, San Marino, Singapore, Slovakia, Slovenia, Spain, Sweden, Switzerland, Turkey, Ukraine, United Kingdom, USA, Vatican City

Scope of supply:
THERMOMARK GO, case, battery, power supply unit incl. 4 adapters, USB cable, MM-EML (20X8)R C1 WH/BK, brief instructions

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- Operated entirely via digital devices using the MARKING system app
- User-friendly operation with context-based menu navigation of the MARKING system app and Application Wizards for easily creating application-specific marking solutions
- The THERMOMARK GO prints materials in cartridge format, which contain the material to be marked and the appropriate ink ribbon
- Easy material change with the uniform GO SERIES cartridge system
- Alternative control via the PROJECT complete software
- Everything needed, always available in the field: The case has sufficient space for your printing system, including accessories and for 9 material cartridges
- Ideal protection of your printing system in all everyday situations thanks to resistant materials and a securely closing buckle
- Easy and efficient storage and transportation of your mobile printing system
- Maximum flexibility for all transport situations with the proven L-BOXX system



Commercial data

Item number	1221548
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1222
GTIN	4063151309268
Weight per piece (including packing)	3,411 g
Weight per piece (excluding packing)	3,411 g
Customs tariff number	84433210
Country of origin	CN

THERMOMARK GO SET - Thermal transfer printer set

1221548

https://www.phoenixcontact.com/us/products/1221548

Set consists of

THERMOMARK GO - Thermal transfer printer

1090747

https://www.phoenixcontact.com/us/products/1090747



Thermal transfer printer, weight: 0.743 kg, length: 0.07 m, width: 135 mm, height: 175 mm, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

THERMOMARK GO ACCU - Battery

0805009

https://www.phoenixcontact.com/us/products/0805009



Battery for mobile operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

THERMOMARK GO ADAPTER - Power supply unit

0805010

https://www.phoenixcontact.com/us/products/0805010



Power supply unit incl. 4 adapters for operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

MM-EML (20X8)R C1 WH/BK - Label

1116204

https://www.phoenixcontact.com/us/products/1116204



Label, Roll, white (RAL 9010), unmarked, can be labeled with: THERMOMARK GO, mounting type: adhesive, Number of individual labels: 297, text field height: 8 mm, text field width: 20 mm, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

THERMOMARK GO CASE - Case

1229456

https://www.phoenixcontact.com/us/products/1229456



Practical and robust case for storing the THERMOMARK GO and THERMOMARK GO.K mobile printers as well as accessories. The case offers space for 9 material cartridges and maximum flexibility for all transport situations thanks to the proven L-BOXX system.

Technical data

Product properties

Product type	Marking system
Scope of supply	THERMOMARK GO, case, battery, power supply unit incl. 4 adapters, USB cable, MM-EML (20X8)R C1 WH/BK, brief instructions

Marking

Identification technology	Thermal transfer

Device properties

Print width	22 mm
Print resolution	203 dpi
Operating system	Windows 10, Windows Server 2016, Windows Server 2019, Windows Server 2022

System properties

Operating system	Windows 10, Windows Server 2016, Windows Server 2019, Windows Server 2022

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)

Dimensions

Width	357 mm
Height	117 mm
Length	442 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 40 °C

Classifications

ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

ETIM

ETIM 10.0	EC001684

UNSPSC

UNSPSC 21.0	43212100

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com