

UCS WM-MP 237-195 7035 - Adapter plate



1225404

<https://www.phoenixcontact.com/us/products/1225404>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter for attaching UCS housings in size 237-195 to the wall, to VESA standard brackets, and to wall outlet boxes, housing is snapped on, material: polycarbonate, color: light gray, similar to RAL 7035



Your advantages

- Flexible in use: Only one bracket for the widest range of applications
- No tools required: UCS housings simply snap on
- Wide range of applications: Use on mounts in accordance with the VESA standard and on cavity sockets with a diameter of 60 mm

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1225404 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC03 |
| Product key | ACFCAZ |
| GTIN | 4063151317171 |
| Weight per piece (including packing) | 252.9 g |
| Weight per piece (excluding packing) | 197.15 g |
| Customs tariff number | 84879090 |
| Country of origin | CN |

UCS WM-MP 237-195 7035 - Adapter plate

1225404

<https://www.phoenixcontact.com/us/products/1225404>

Technical data


Notes

| | |
|---------------|--|
| Assembly note | Please observe the assembly instructions available in the download area. |
|---------------|--|

Product properties

| | |
|----------------|--------------------|
| Product type | Adapter plate |
| Housing type | Universal housings |
| Housing series | UCS |
| Product family | UCS 237-195 |

Dimensions

| | |
|---------------------|---|
| Dimensional drawing |  |
| Width | 240.3 mm |
| Height | 202.8 mm |
| Depth | 17.9 mm |

Material specifications

| | |
|--|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
| Material | PC |
| Flammability rating according to UL 94 | V0 |
| CTI according to IEC 60112 | 225 |
| Insulating material | PC |

Environmental and real-life conditions

Vibration test

| | |
|------------------------|-----------------------------|
| Specification | IEC 60068-2-6:2007-12 |
| Frequency | 10 - 150 - 10 Hz |
| Sweep speed | 1 octave/min |
| Amplitude | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration | 2g (58.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h |
| Test directions | X-, Y- and Z-axis |

Glow-wire test

| | |
|------------------|------------------------|
| Specification | IEC 60695-2-11:2014-02 |
| Temperature | 850 °C |
| Time of exposure | 30 s |

UCS WM-MP 237-195 7035 - Adapter plate



1225404

<https://www.phoenixcontact.com/us/products/1225404>

Thermal stability / ball thrust test

| | |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature | 125 °C |
| Test duration | 1 h |
| Force | 20 N |

Mechanical strength / tumbling barrel

| | |
|----------------|------------------------|
| Specification | IEC 60068-2-31:2008-05 |
| Height of fall | 50 cm |
| Frequency | 50 |

Shocks

| | |
|--------------------------------|-----------------------------------|
| Specification | IEC 60068-2-27:2008-02 |
| Pulse shape | Half-sine |
| Acceleration | 15g |
| Shock duration | 11 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |

Test for substances that would hinder coating with paint or varnish

| | |
|---------------|----------------------|
| Specification | VW PV 3.10.7:2005-02 |
| Result | Test passed |

Ambient conditions

| | |
|---|-------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 95 % |

Mounting

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Packaging specifications

| | |
|-------------------|---------------|
| Type of packaging | Box packaging |
|-------------------|---------------|


UCS WM-MP 237-195 7035 - Adapter plate

1225404

<https://www.phoenixcontact.com/us/products/1225404>



Drawings



Schematic representation – for additional information, see product range drawing in the Download Center

UCS WM-MP 237-195 7035 - Adapter plate



1225404

<https://www.phoenixcontact.com/us/products/1225404>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1225404>



UL Recognized

Approval ID: E240868

UCS WM-MP 237-195 7035 - Adapter plate



1225404

<https://www.phoenixcontact.com/us/products/1225404>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UCS WM-MP 237-195 7035 - Adapter plate



1225404

<https://www.phoenixcontact.com/us/products/1225404>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Perfluorobutane sulfonic acid (PFBS) and its salts(CAS: n/a) |
| SCIP | 4d02d4a0-9cca-4702-ab36-546ade23b0ac |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com