ES-FT-C4M-CO1 - Device connector front mounting

1231071

https://www.phoenixcontact.com/us/products/1231071

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRIMP



Device connector front mounting, Range of articles: BPP, color: red/black, number of positions: 1, min. conductor cross-section: 2.5 mm^2, max. conductor cross-section: 6 mm^2, rated voltage: 1500 V DC, rated current: 26 A, Connection method: Crimp, max. cable diameter: 5.8 mm

Commercial data

Item number	1231071
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	AB04
Product key	ABLDAB
GTIN	4063151331542
Weight per piece (including packing)	8.128 g
Weight per piece (excluding packing)	5.826 g
Customs tariff number	85359000
Country of origin	IN

Technical data

Product properties

Product type	Connectors for energy storage
Product family	BPP
Number of positions	1

Insulation characteristics

Protection class	II
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	1500 V
Rated voltage	1500 V DC in accordance with IEC 62852:2014/AMD1:2020
Rated surge voltage	16 kV
Rated surge voltage (III/3)	16 kV
Rated current (2.5 mm²)	26 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (4.0 mm²)	32 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (6.0 mm²)	38 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (10 mm²)	50 A (in accordance with IEC 62852:2014/AMD1:2020)
Contact resistance	< 0.45 mΩ (depending on the mating connector used)

Connection data

Stripping length	8 mm

Dimensions

Width	21 mm
Height	27.4 mm
Length	49.2 mm

Material specifications

Color	red/black
Color of the housing part	black
Material Seal	EPDM
Material Housing	PPE
Flammability rating according to UL 94	V0
Insulating material group	I
Material for screw connection	PA

Cable/line

External cable diameter	5.8 mm
Single wire, cross section	2.5 mm² 6 mm²
Halogen-free	yes

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	100
Insertion force	< 45 N ±10 N

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/IP68 (2 m / 24 h) (plugged in)
	IP20 (Not plugged in)
	IP66/IP68 (2 m / 24 h)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-25 °C ... 50 °C

Standards and regulations

Standards/specifications	IEC 62852/UL 6703

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1231071

TÜV Rheinland
Approval ID: R 60178082_0001

UL Recognized
Approval ID: E477377-20250305

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	1500 V	50 A	14 - 10	-

Classifications

ECLASS

ECLASS-13.0	27440107
ECLASS-15.0	27440107

ETIM

ETIM 10.0	EC002635

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)
SCIP	1ff15c81-1afb-4c44-848f-636d16170dc9

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com