

# TM-RIBBON 40 BK 105 - Ink ribbon



1259008

<https://www.phoenixcontact.com/us/products/1259008>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ink ribbon, for the E-WMS... product group in combination with the THERMOMARK E.SLEEVE applicator and the WMS... and WMS-2 HF... product groups in combination with conventional roll printers, length: 300 m, roll length: 300 m, width: 40 mm, color: black

## Product description

The TM-RIBBON 40 BK 105 is a thermal transfer ink ribbon, which is suitable for automated processing with the THERMOMARK E.SLEEVE applicator in combination with the THERMOMARK E.300 (D) / 600 (D) printers and the markers from the E-WMS... product family. Alternatively, the ink ribbon can also be used without the applicator for the identification of the E-WMS material or the WMS... and WMS-2 HF... product groups

## Your advantages

- The TM-RIBBON 40 BK 105 thermal transfer ink ribbon is suitable for automated processing with the THERMOMARK E.SLEEVE applicator
- For efficient use of the entire ink ribbon, the width is optimally tailored to the E-WMS..., WMS..., and WMS-2 HF... product groups
- When combined with the right shrink sleeve, the printing is highly resistant to solvents and mechanical influences

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1259008       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG02          |
| Product key                          | BG1223        |
| GTIN                                 | 4063151367978 |
| Weight per piece (including packing) | 136.6 g       |
| Weight per piece (excluding packing) | 136.6 g       |
| Customs tariff number                | 96121010      |
| Country of origin                    | JP            |

# TM-RIBBON 40 BK 105 - Ink ribbon



1259008

<https://www.phoenixcontact.com/us/products/1259008>

## Technical data

### Product properties

|                 |            |
|-----------------|------------|
| Product type    | Ink ribbon |
| Scope of supply | Ink ribbon |

### Marking

|                           |                  |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

### Dimensions

|                |       |
|----------------|-------|
| Width          | 40 mm |
| Length         | 300 m |
| Length of roll | 300 m |

### Material specifications

|          |                                   |
|----------|-----------------------------------|
| Color    | black (RAL 9005)                  |
| Material | Polyolefin-compatible ink coating |

# TM-RIBBON 40 BK 105 - Ink ribbon



1259008

<https://www.phoenixcontact.com/us/products/1259008>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19140614 |
| ECLASS-15.0 | 19140614 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001694 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 44103100 |
|-------------|----------|

# TM-RIBBON 40 BK 105 - Ink ribbon



1259008

<https://www.phoenixcontact.com/us/products/1259008>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)