

# RCK-TGUM/BL16+3/10,0PUR-UX - Master cable



1260764

<https://www.phoenixcontact.com/us/products/1260764>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Master cable, application: Sensor/actuator box, number of positions: 19, slot assignment: Double, status display: no; master cable connection: M23 plug connection, PUR/PVC, cable length: 10 m, shielding: no, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %). This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

## Commercial data

Item number	1260764
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB34
Product key	ABRDCA
GTIN	4063151414740
Weight per piece (including packing)	1,940 g
Weight per piece (excluding packing)	1,920.895 g
Customs tariff number	85444290
Country of origin	DE

1260764

<https://www.phoenixcontact.com/us/products/1260764>

## Technical data

### Notes

Notes on operation	The master cable is earmarked for use on the sensor/actuator boxes with an M23 plug-in connection.
--------------------	--

### Product properties

Product type	Master cable, assembled
Application	Sensor/actuator box
Number of positions	19

### Electrical properties

Nominal voltage $U_N$	48 V AC
	60 V DC

### Connection data

Connection method	Fixed connection
-------------------	------------------

### Signaling

Status display present	no
------------------------	----

### Material specifications

Material Housing	PUR
Material of contact, master cable side	CU alloy
Material of the contact carrier on the master cable side	PA
Material of contact surface, master cable side	gold-plated

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M23

#### Connection 2

Head design	free cable end
-------------	----------------

### Cable/line

Cable length	10 m
--------------	------


PUR/PVC black [PUR]

# RCK-TGUM/BL16+3/10,0PUR-UX - Master cable



1260764

<https://www.phoenixcontact.com/us/products/1260764>

Dimensional drawing	
Cable weight	183.7 kg/km
UL AWM Style	20549 (80°C/300 V)
Number of positions	19
Shielded	no
Cable type	PUR/PVC black [PUR]
Conductor structure signal line	28x 0.15 mm
AWG signal line	20
Conductor structure, voltage supply	56x 0.15 mm
AWG power supply	17
Conductor cross-section	16x 0.5 mm <sup>2</sup> (Signal line) 3x 1 mm <sup>2</sup> (power line)
Wire diameter incl. insulation	1.5 mm ±0.1 mm (Signal line) 2.1 mm ±0.1 mm (power line)
External cable diameter	10.50 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet, gray/pink, red/blue, white/green, brown/green, white/yellow, yellow/brown, white/gray, gray/brown
Inner sheath thickness	≥ 0.15 mm
Thickness, outer sheath	≥ 0.76 mm
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V
Test voltage	2000 V
Minimum bending radius, fixed installation	7.5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	79 mm
Smallest bending radius, movable installation	105 mm
Dynamic load capacity (bending)	Max. bending cycles: 1500000, Bending radius: 10 x D, Traversing path: 2 m, Traversing rate: 2 m/s
Flame resistance	according to DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free

# RCK-TGUM/BL16+3/10,0PUR-UX - Master cable



1260764

<https://www.phoenixcontact.com/us/products/1260764>

Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)


## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 °C ... 125 °C (Plug / socket)

Drawings

Schematic diagram



Pin assignment M23 socket, 19-pos., female side view

1260764

<https://www.phoenixcontact.com/us/products/1260764>

Circuit diagram



Circuit diagram

# RCK-TGUM/BL16+3/10,0PUR-UX - Master cable



1260764

<https://www.phoenixcontact.com/us/products/1260764>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1260764>



**EAC**

Approval ID: 19060508

# RCK-TGUM/BL16+3/10,0PUR-UX - Master cable



1260764

<https://www.phoenixcontact.com/us/products/1260764>

## Classifications

### ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# RCK-TGUM/BL16+3/10,0PUR-UX - Master cable



1260764

<https://www.phoenixcontact.com/us/products/1260764>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)