

# BL2 BPC 1541E-8/0 - Box PC



1272829

<https://www.phoenixcontact.com/us/products/1272829>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Atom® E3940 processor



## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1272829       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DR12          |
| Product key                          | DRBABA        |
| GTIN                                 | 4063151465032 |
| Weight per piece (including packing) | 934 g         |
| Weight per piece (excluding packing) | 762 g         |
| Customs tariff number                | 84715000      |
| Country of origin                    | TW            |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|              |        |
|--------------|--------|
| Product type | Box PC |
|--------------|--------|

#### Computer data

|                  |                            |
|------------------|----------------------------|
| Processor        | Intel® Atom™ E3940 1.6 GHz |
| Operating system | without operating system   |
| RAM              | 8 GB LPDDR4                |
| Cooling          | passive                    |

#### Display

|              |      |
|--------------|------|
| Display type | none |
|--------------|------|

### System properties

|               |                       |
|---------------|-----------------------|
| User software | without user software |
|---------------|-----------------------|

### Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 16.8 W |
|---|--------|

#### Supply

|                             |   |
|-----------------------------|---|
| Supply voltage (DC)         | 24 V DC ±20% (CE rating)  |
| Supply voltage range        | 12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC) |
| Max. current consumption    | 0.7 A (24 V DC)   |
| Typical current consumption | 0.53 A (24 V DC)  |

### Connection data

#### Power supply

|                                   |  |
|-----------------------------------|--|
| Connection method                 | Screw connection                             |
| Conductor cross-section, rigid    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section, flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG       | 28 ... 16                                    |
| Stripping length                  | 7 mm   |

### Interfaces

|             |                                      |
|-------------|--------------------------------------|
| Interfaces  | 1x DP++                              |
|             | 2x USB 3.0                           |
|             | 2x COM ports                         |
| Network     | 2x Ethernet (10/100/1000 Mbps), RJ45 |
| LAN chipset | Intel® I210-AT                       |

1272829

<https://www.phoenixcontact.com/us/products/1272829>

## Dimensions

### External dimensions

|                        |                       |
|------------------------|-----------------------|
| Width / Height / Depth | 99 mm / 92 mm / 63 mm |
|------------------------|-----------------------|

## Environmental and real-life conditions

### Ambient conditions

|   |  |
|---|--|
| Degree of protection                    | IP30   |
| Ambient temperature (operation)         | -20 °C ... 60 °C (with 0.5 m/s airflow)      |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                             |
| Permissible humidity (operation)        | 5 % ... 85 % (non-condensing)                |
| Shock                                   | 15g, 11 ms in accordance with IEC 60068-2-27 |
| Vibration (operation)                   | 1g, according to EN 60068-2-6                |

## Approvals

### Conformity/Approvals

|             |              |
|-------------|--------------|
| Conformance | CE-compliant |
|-------------|--------------|

## Mounting

|               |                                       |
|---------------|---------------------------------------|
| Mounting type | DIN rail mounting                     |
|               | Panel mounting (Accessories required) |

# BL2 BPC 1541E-8/0 - Box PC



1272829

<https://www.phoenixcontact.com/us/products/1272829>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1272829>



### IECEE CB Scheme

Approval ID: US-39601-M1-UL



### UL Listed

Approval ID: E238705 D12:D1050



### cUL Listed

Approval ID: E238705 D12:D1050

# BL2 BPC 1541E-8/0 - Box PC



1272829

<https://www.phoenixcontact.com/us/products/1272829>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19200102 |
| ECLASS-15.0 | 19200102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001413 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211500 |
|-------------|----------|

1272829

<https://www.phoenixcontact.com/us/products/1272829>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes                |
| Exemption                               | 6(c), 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-15   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 77d28f4e-7610-4539-9beb-dd30547c1391 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)