

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Battery module (device with battery), VRLA-AGM, 24 V DC, 12 Ah, automatic detection and communication with QUINT UPS-IQ

## Product description

For continuous monitoring and intelligent management, there is constant communication with the QUINT UPS. Thanks to automatic detection of the battery module and tool-free switching during operation, quick installation is possible. The battery modules for QUINT UPS with IQ Technology are fully charged before being sent to our warehouse.

## Your advantages

- Maximum buffer times
- Lead AGM (Absorbent Glass Mat) technology

## Commercial data

Item number	1274119
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM24
Product key	CMUEV3
GTIN	4063151466510
Weight per piece (including packing)	9,930 g
Weight per piece (excluding packing)	9,400 g
Customs tariff number	85072080
Country of origin	MY

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Technical data

### Notes

#### General

Note on the battery	This product contains a battery with a limited shelf life that must be charged every few months. The product packaging indicates when the battery must be started up or recharged. The general shelf life can be found in the energy storage devices area under "Latest startup".
---------------------	---

### Energy storage

#### Input

Input voltage	24 V DC (SELV)
Nominal capacity	min. 12 Ah
Charging current	3.6 A
End-of-charge voltage	27.6 V DC (20 °C)

#### Output

Output voltage	24 V DC
Output current	max. 50 A
Output fuse	2x 25 A
Buffer time	21 min (20 A) 8 min (40 A)

#### General

Connection in parallel	yes max. 5
Connection in series	no
Battery type	BB Battery BP 12-12FR LEOCH LHR 1255W
Battery technology	VRLA-AGM
IQ-Technology	yes
Latest startup date (battery only)	12 Months (-20 °C ... 20 °C) 9 Months (25 °C) 6 Months (30 °C)
Service life	6 Years (20 °C)
Size designation	Block
Battery pack	yes
Suitable for fast charging	yes
Temperature sensor	yes
Number of replacement battery kits	UPS-BAT-KIT/PB/2X12V/12AH (1283121) UPS-BAT-KIT/PB/2X12V/12AH/L (1859169)

### Connection data

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Battery

Position	4.x
----------	-----

## Connection technology

Position marking	4.1 (+), 4.2 (-)
------------------	------------------

## Conductor connection

Connection method	Screw connection
rigid	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup>
	10 mm <sup>2</sup> ... 16 mm <sup>2</sup> (recommended)
flexible	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup>
	10 mm <sup>2</sup> ... 16 mm <sup>2</sup> (recommended)
flexible with ferrule without plastic sleeve	10 mm <sup>2</sup> ... 16 mm <sup>2</sup> (recommended)
flexible with ferrule with plastic sleeve	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup>
AWG	20 ... 6
	8 ... 6 (recommended)
Stripping length	10 mm (recommended)
	10 mm
Tightening torque	1.2 Nm ... 1.5 Nm
	15 lb <sub>F</sub> -in.
Drive form screw head	Slotted L

## LIN

Position	4.x
----------	-----

## Connection technology

Position marking	4.3 (┘┘  )
------------------	---

## Conductor connection

Connection method	Screw connection
rigid	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup> (LIN)
flexible	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup> (LIN)
flexible with ferrule without plastic sleeve	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup> (LIN)
flexible with ferrule with plastic sleeve	0.75 mm <sup>2</sup> ... 16 mm <sup>2</sup> (LIN)
AWG	20 ... 6 (LIN)
Stripping length	10 mm (LIN)
Tightening torque	1.2 Nm ... 1.5 Nm (LIN)
	15 lb <sub>F</sub> -in. (LIN)
Drive form screw head	Slotted L

## Product properties

Product type	Battery module
Product family	Battery module (device with battery)
Application	for QUINT4 DC-UPS, QUINT4 AC-UPS, QUINT-UPS, and TRIO-UPS-2G
Disposal	Used batteries must not be thrown away with household waste,

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

they should instead be disposed of in accordance with applicable national regulations.

## Insulation characteristics

Protection class	III
Degree of pollution	2

## Dimensions

### Item dimensions

Width	202 mm
Height	202 mm
Depth	110 mm

### Drill hole

Diameter	5 mm
----------	------

### Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	5 mm / 5 mm

## Mounting

Mounting type	Panel mounting, optional DIN rail mounting
---------------	--

## Material specifications

Housing material	Metal
Type of housing	Galvanized sheet steel, powder-coated

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (storage/transport)	-20 °C ... 40 °C
Ambient temperature (charge)	0 °C ... 40 °C
Ambient temperature (discharge)	-20 °C ... 50 °C
Max. permissible relative humidity (operation)	≤ 95 %
Shock	15g, 11 ms, in each space direction (in accordance with IEC 60068-2-27)
Vibration (operation)	5 Hz ... 100 Hz, 0.7g (in accordance with DNV / IEC 60068-2-6)

## Approvals

### UL

Identification	UL/C-UL Listed UL 61010-1
----------------	---------------------------

### UL

Identification	UL/C-UL Listed ANSI/UL 121201 Class I, Division 2, Groups A, B, C, D (Hazardous Location)
----------------	---

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Shipbuilding

Identification	DNV
----------------	-----

## Shipbuilding

Identification	ABS
----------------	-----

## Shipbuilding

Identification	LR
----------------	----

## Shipbuilding

Identification	BV
----------------	----

## Ex data

Suited for EX-applications	no
----------------------------	----



# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Graphic

Load Current	Buffertime																			
	Minutes										Hours									
	1	2	3	5	10	20	30	40	45	50	1	2	3	5	8	10	15	24	40	60
15 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
35 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
55 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
90 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
125 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
180 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
275 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red
400 W	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Yellow	Orange	Orange	Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red	Dark Red

The data is based on an ambient temperature of +25 °C at the start of use.

- 1274117 UPS-BAT/PB/24DC/4AH
- 1274119 UPS-BAT/PB/24DC/12AH
- 1354641 UPS-BAT/PB/24DC/40AH
- 1274118 UPS-BAT/PB/24DC/7AH
- 1348516 UPS-BAT/PB/24DC/20AH
- 1474660 UPS-BAT/PB/24DC/110AH

Lead battery buffer times for QUINT AC UPS 500 VA

## Graphic

Load Current	Buffertime																											
	Minutes														Hours													
	1	2	3	4	5	8	10	15	20	25	30	40	50	1	1.5	2	3	4	6	9	10	15	20	24	40			
100 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
200 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
300 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
400 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
500 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
600 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
700 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
800 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			
900 W	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x	2x			

2x: There are always two battery modules of the same capacity are required. The data is based on an ambient temperature of +25 °C at the start of use.

- 1274117 UPS-BAT/PB/24DC/4AH
- 1274119 UPS-BAT/PB/24DC/12AH
- 1354641 UPS-BAT/PB/24DC/40AH
- 1274118 UPS-BAT/PB/24DC/7AH
- 1348516 UPS-BAT/PB/24DC/20AH
- 1474660 UPS-BAT/PB/24DC/110AH

Buffer times for QUINT AC UPS 1 kVA

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1274119>

### ABS

Approval ID: 22-2244289-PDA



### EAC

Approval ID: RU\*DE\*01.B.78948/21



### cULus Listed

Approval ID: FILE E 123528



### LR

Approval ID: LR22136091TA



### BV

Approval ID: 41516/B0 BV

### DNV

Approval ID: TAA0000265



### IECEE CB Scheme

Approval ID: DK-134807-A1-UL



### IECEE CB Scheme

Approval ID: DK-134807-A1-UL



### EAC

Approval ID: RU\*DE\*01.B.78948/21

### ABS

Approval ID: 22-2244289-PDA



### BV

Approval ID: 41516/B0 BV

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>



**LR**

Approval ID: LR22136091TA



**cULus Listed**

Approval ID: FILE E 123528

**DNV**

Approval ID: TAA0000265



**cULus Listed**

Approval ID: FILE E 199827



**cULus Listed**

Approval ID: FILE E 199827

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Classifications

### ECLASS

ECLASS-13.0	27050403
ECLASS-15.0	27050403

### ETIM

ETIM 10.0	EC003893
-----------	----------

### UNSPSC

UNSPSC 21.0	26111700
-------------	----------

# UPS-BAT/PB/24DC/12AH - Battery module



1274119

<https://www.phoenixcontact.com/us/products/1274119>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-8
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
	Lead monoxide (lead oxide)(CAS: 1317-36-8)
	Lead(CAS: 7439-92-1)
SCIP	e5ec962e-167d-425b-85e2-113ddb104ff8

### EF3.1 Climate Change

CO2e kg	30.3 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)