

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting



1239956

<https://www.phoenixcontact.com/us/products/1239956>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 4-position, Socket, straight, M12-SPEEDCON, D-coding, THR solder connection, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1239956
Packing unit	60 pc
Minimum order quantity	60 pc
Product key	ABQAIA
GTIN	4063151457228
Weight per piece (including packing)	11.422 g
Weight per piece (excluding packing)	8.952 g
Country of origin	DE

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting



1239956

<https://www.phoenixcontact.com/us/products/1239956>

Technical data

Mounting

Mounting type	Rear mounting (M12 x 1, with flat nut)
---------------	--

Product properties

Product type	Circular connectors (device side)
Number of positions	4
Shielded	no
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Material Housing	GD-Zn
Material Housing surface	Ni
Material Insulating body	PPA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM / EPDM
Flammability rating according to UL 94	HB

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A

Connection data

Conductor connection

Connection method	THR solder connection
Contact connection type	Socket

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Head locking type	SPEEDCON

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting



1239956

<https://www.phoenixcontact.com/us/products/1239956>

Coding	D
--------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 85 °C (Plug / socket)

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting

1239956

<https://www.phoenixcontact.com/us/products/1239956>

Drawings

Schematic diagram



Pin assignment M12 socket, 4-pos., D-coded, female side

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting



1239956

<https://www.phoenixcontact.com/us/products/1239956>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1239956>

 UL Recognized Approval ID: E118976-20100522				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	250 V	4 A	22	-

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting



1239956

<https://www.phoenixcontact.com/us/products/1239956>

Classifications

ECLASS

ECLASS-13.0	27440110
ECLASS-15.0	27440110

ETIM

ETIM 10.0	EC003568
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SACC-DSIV-FSD-4CON-L180 SCOTHRX - Device connector rear mounting



1239956

<https://www.phoenixcontact.com/us/products/1239956>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com