

# RC-07P1N129006X - Coupler connector



1240486

<https://www.phoenixcontact.com/us/products/1240486>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows the 12-pos.  
product version

M23, Coupler connector, application: Signal, series: RC, straight, shielded: yes, Screw locking mechanism, No. of pos.: 7, Direction of rotation: Standard, contact connection type: Pin, Solder cup, cable diameter range: 7.5 mm ... 9.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1240486       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 1 pc          |
| Product key                          | ABRAFG        |
| GTIN                                 | 4063151434069 |
| Weight per piece (including packing) | 77.15 g       |
| Weight per piece (excluding packing) | 72.064 g      |
| Country of origin                    | DE            |

# RC-07P1N129006X - Coupler connector



1240486

<https://www.phoenixcontact.com/us/products/1240486>

## Technical data

### Product properties

|              |                                 |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

### Connector

#### Insulating body

|   |  |
|---|--|
| Coding  | N  |
| Material (Insulating body)                      | PBT                                      |
| Material (Contact)                              | CuZn                                     |
| Material (Contact surface)                      | Ni/Au                                    |
| Insertion/withdrawal cycles                     | 50                                       |
| Connection method                               | Solder cup                               |
| Contact switching type                          | Pin                                      |
| Application                                     | Signal                                   |
| Number of positions                             | 7  |
| Direction of rotation                           | Standard                                 |
| Connection profile                              | 7  |
| Number (Contact group 1)                        | 7  |
| Contact diameter (Contact group 1)              | 2 mm                                     |
| Litz wires Min. cross section (Contact group 1) | 0.08 mm <sup>2</sup>                     |
| Litz wires Max. cross section (Contact group 1) | 2.5 mm <sup>2</sup>                      |
| Rated current Contact (Contact group 1)         | 20 A (for max. connection cross section) |
| Rated voltage Contact (Contact group 1)         | 48 V AC<br>74 V DC                       |
| Rated surge voltage                             | 1.5 kV                                   |
| Overvoltage category                            | III                                      |
| Degree of pollution                             | 3  |

#### Housing

|                                   |                         |
|-----------------------------------|-------------------------|
| Type                              | Coupling housing        |
| Thread type                       | M23                     |
| Design                            | straight                |
| Type of locking                   | Screw locking mechanism |
| Pg screw connection               | none                    |
| Material (Housing)                | GD-Zn                   |
| Material (Housing surface)        | Ni                      |
| Material (Rotating parts)         | CuZn                    |
| Degree of protection (plugged in) | IP67                    |

#### Seal

|                         |                   |
|-------------------------|-------------------|
| External cable diameter | 7.5 mm ... 9.5 mm |
|-------------------------|-------------------|


# RC-07P1N129006X - Coupler connector

1240486

<https://www.phoenixcontact.com/us/products/1240486>

## Drawings

Schematic diagram




Connector pin assignment

# RC-07P1N129006X - Coupler connector

1240486

<https://www.phoenixcontact.com/us/products/1240486>

Schematic diagram



Connector pin assignment

# RC-07P1N129006X - Coupler connector



1240486

<https://www.phoenixcontact.com/us/products/1240486>

Schematic diagram



Dimensional drawing

# RC-07P1N129006X - Coupler connector



1240486

<https://www.phoenixcontact.com/us/products/1240486>

## Classifications

### ECLASS

ECLASS-13.0

27440116

### ETIM

ETIM 9.0

EC002635

# RC-07P1N129006X - Coupler connector



1240486

<https://www.phoenixcontact.com/us/products/1240486>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)