


BL2-2,54/16-ST - Power plug

1281276

<https://www.phoenixcontact.com/us/products/1281276>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector for DIN rail bus connector with 16 free cable ends with a cross section of 0.25 mm², 500 mm long, female contacts

Commercial data

Item number	1281276
Packing unit	100 pc
Minimum order quantity	50 pc
Sales key	AC10
Product key	ACHBBZ
GTIN	4063151479817
Weight per piece (including packing)	34.59 g
Weight per piece (excluding packing)	34 g
Customs tariff number	85444290
Country of origin	TW

BL2-2,54/16-ST - Power plug



1281276

<https://www.phoenixcontact.com/us/products/1281276>

Technical data

Product properties

Product type	Cable set
Product family	HBUS16
Number of positions	16
Pitch	2.54 mm
Pin layout	Linear pinning

Electrical properties

Properties

Nominal current I_N	3 A (Total current of 25 A max.)
Rated voltage (III/3)	48 V
Rated surge voltage (III/3)	0.8 kV
Rated voltage (III/2)	48 V
Rated surge voltage (III/2)	0.8 kV
Rated surge voltage (II/2)	0.8 kV

Connection data

Maximum load current	3 A (maximum total current 23 A)
----------------------	----------------------------------

Dimensions

Pitch	2.54 mm
Length [l]	500 mm

Material specifications

Material data - contact

Contact material	Cu alloy
------------------	----------

Material data - housing

Color (Housing)	black (9005)
Insulating material	Nylon
Flammability rating according to UL 94	V0

Connector

Connection 1

Insulating material	Nylon
---------------------	-------

Electrical tests

Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Rated insulation voltage (III/3)	48 V

BL2-2,54/16-ST - Power plug



1281276

<https://www.phoenixcontact.com/us/products/1281276>

Rated surge voltage (III/3)	0.8 kV
Rated insulation voltage (III/2)	48 V
Rated surge voltage (III/2)	0.8 kV
Rated surge voltage (II/2)	0.8 kV

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

Mounting

Pin layout	Linear pinning
------------	----------------

Packaging specifications

Type of packaging	PE bag
-------------------	--------

BL2-2,54/16-ST - Power plug




1281276

<https://www.phoenixcontact.com/us/products/1281276>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1281276>

 cULus Recognized Approval ID: E118976-20090923				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	30 V	2 A	-	-

BL2-2,54/16-ST - Power plug



1281276

<https://www.phoenixcontact.com/us/products/1281276>

Classifications

ECLASS

ECLASS-13.0	27460202
ECLASS-15.0	27460202

ETIM

ETIM 10.0	EC002638
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

BL2-2,54/16-ST - Power plug



1281276

<https://www.phoenixcontact.com/us/products/1281276>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com