

CA-17S1N12T007SX - Cable connector



1243496

<https://www.phoenixcontact.com/us/products/1243496>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

M23, Cable connector, application: Signal, series: CA, angled, shielded: yes, SPEEDCON, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 6 mm ... 10 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)



The figure shows the 12-pos. product version

Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1243496 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Product key | ABRAED |
| GTIN | 4063151402037 |
| Weight per piece (including packing) | 184.275 g |
| Weight per piece (excluding packing) | 184.275 g |
| Country of origin | DE |

CA-17S1N12T007SX - Cable connector



1243496

<https://www.phoenixcontact.com/us/products/1243496>

Technical data

Product properties

| | |
|--------------|---------------------------------|
| Product type | Circular connector (cable-side) |
|--------------|---------------------------------|

Connector

Connection 1

| | |
|-------------|--------|
| Head design | Socket |
|-------------|--------|

Insulating body

| | |
|---|--------------------|
| Coding | N |
| Material (Insulating body) | PBT |
| Material (Contact) | CuZn |
| Material (Contact surface) | Ni/Au |
| Insertion/withdrawal cycles | 100 |
| Connection method | Solder connection |
| Contact switching type | Socket |
| Application | Signal |
| Number of positions | 17 |
| Direction of rotation | Standard |
| Connection profile | 17 |
| Number (Power contacts) | 0 |
| Rated voltage Contact (Power contacts) | 48 V AC 74 V DC |
| Rated surge voltage | 1.5 kV |
| Overvoltage category | III |
| Degree of pollution | 3 |
| Number (Signal contacts) | 17 |
| Contact diameter (Signal contacts) | 1 mm |
| Litz wires Max. cross section (Signal contacts) | 1 mm ² |
| Rated current Contact (Signal contacts) | 8 A |

Housing

| | |
|-----------------------------------|-------------------------|
| Type | Cable connector housing |
| Thread type | M23 |
| Design | angled |
| Type of locking | SPEEDCON |
| Pg screw connection | none |
| Housing material | Metal |
| Degree of protection (plugged in) | IP67 |

Seal

| | |
|-------------------------|----------------|
| External cable diameter | 6 mm ... 10 mm |
| Seal material | NBR |

CA-17S1N12T007SX - Cable connector



1243496

<https://www.phoenixcontact.com/us/products/1243496>

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Permissible humidity (storage/transport) | 50 % ... 65 % |

CA-17S1N12T007SX - Cable connector



1243496

<https://www.phoenixcontact.com/us/products/1243496>

Drawings

Schematic diagram



Connector pin assignment

CA-17S1N12T007SX - Cable connector

1243496

<https://www.phoenixcontact.com/us/products/1243496>



Schematic diagram



Connector pin assignment

CA-17S1N12T007SX - Cable connector



1243496

<https://www.phoenixcontact.com/us/products/1243496>

Classifications

ECLASS

ECLASS-13.0

27440116

ETIM

ETIM 9.0

EC002635

UNSPSC

UNSPSC 21.0

39121100

CA-17S1N12T007SX - Cable connector



1243496

<https://www.phoenixcontact.com/us/products/1243496>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com