

# WP 6121-WXPS - Web panel



1290802

<https://www.phoenixcontact.com/us/products/1290802>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP66 Touch panel with 12.1-inch widescreen (16:9) XGA, PCAP display, Software: Qt Browser



## Your advantages

- Easy startup – just enter the IP and URL
- Flexible, thanks to open web standard and free choice of web server and visualization software
- No security updates are required for JAVA or Flash plug-ins thanks to HTML5
- Ideal for use with PLCnext Engineer or CODESYS
- Embedded Linux operating system
- Visualization of self-programmed JavaScript applications possible

## Commercial data

Item number	1290802
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR17
Product key	DRCADF
GTIN	4063151522650
Weight per piece (including packing)	4,000 g
Weight per piece (excluding packing)	2,200 g
Customs tariff number	84714100
Country of origin	TW

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Operator panel
--------------	----------------

#### Computer data

Processor	Arm® Cortex®-A53, 1.6 GHz
Operating system	Yocto/Linux®
Data storage system	Flash eMMC, 8 GB
Slots	1x microSD

#### Display

Display type	30.7 cm / 12.1"-TFT
Screen resolution	1280 x 800 Pixel(s) (WXGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	400 cd/m², typical (adjustable)
MTBF	50000 h
Color spectrum	16.7 million colors
Reading angle left	88.00 °
Reading angle right	88.00 °
Reading angle top	88.00 °
Reading angle bottom	88.00 °

### Interfaces

Interfaces	2x USB 2.0
	1x USB 3.0, Typ C
	1x COM (RS-232/422/485)
Optional interfaces	Without optional interface
Network	1 x Ethernet (10/100/1000 Mbps), RJ45
Bus system	without bus system

### System properties

User software	QT browser
---------------	------------

#### System requirements

Runtime system	Qt Browser
----------------	------------

### Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

## Supply

Supply voltage (DC)	24 V DC $\pm$ 20%
Supply voltage range	18 V DC ... 32 V DC
Power supply unit	24 V DC $\pm$ 20 %
Max. current consumption	1.81 A (24 V DC)
Typical current consumption	0.9 A (24 V DC)

## Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

## Mounting

Mounting type	Front mounting
---------------	----------------

## Material specifications

Color (Housing)	white aluminium (RAL 9006)
Material front plate	Aluminum (natural anodized)
Housing material	Aluminum cast alloy, powder-coated

## Connection data

Connection method	Screw connection
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C
Permissible humidity (operation)	5 % ... 85 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 85 % (non-condensing)
Shock	15g with 11 ms impulse
Vibration (operation)	1g

## Dimensions

### External dimensions

Width / Height / Depth	302 mm / 229 mm / 51 mm (Dimensions of the front plate)
------------------------	---

### Installation dimensions

Width / Height / Installation depth	292 mm / 219 mm / (Installation cutout)
-------------------------------------	---

1290802

<https://www.phoenixcontact.com/us/products/1290802>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1290802>



**IECEE CB Scheme**  
Approval ID: US-39088-UL



**UL Listed**  
Approval ID: E238705



**cUL Listed**  
Approval ID: E238705



**IECEE CB Scheme**  
Approval ID: US-39088-UL



**cUL Listed**  
Approval ID: E238705



**UL Listed**  
Approval ID: E238705

1290802

<https://www.phoenixcontact.com/us/products/1290802>

## Classifications

### ECLASS

ECLASS-13.0	27330201
ECLASS-15.0	27330201

### ETIM

ETIM 10.0	EC001412
-----------	----------

### UNSPSC

UNSPSC 21.0	43211900
-------------	----------

1290802

<https://www.phoenixcontact.com/us/products/1290802>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

### EF3.1 Climate Change

CO2e kg	167.775 kg CO2e
---------	-----------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)