

# MACX MCR-EX-AP-2REL-2DI-LP-SP - Relay module



1292332

<https://www.phoenixcontact.com/us/products/1292332>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-Relay module isolates binary Ex i and non Ex i signal and control circuits, and is used for intrinsically safe activation of Ex i field currents via one changeover contact relay per channel.  
number of channels: 2, Standard configuration, Loop-powered, 4-way isolation, Safety Integrity Level (SIL, IEC 61508): 2, Push-in connection

## Commercial data

Item number	1292332
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C430
Product key	DK121W
GTIN	4063151525453
Weight per piece (including packing)	178.5 g
Weight per piece (excluding packing)	160 g
Customs tariff number	85437090
Country of origin	DE

## Technical data

### Notes

Notes on operation	Installation conditions influence the ambient temperature. Please refer to the operating instructions.
--------------------	--

### Product properties

Product type	Relay Module
Product family	MACX Analog
No. of channels	2

### Electrical properties

Electrical isolation	4-way isolation
Electrical isolation between input and output	yes

#### Electrical isolation Input/output IEC/EN 60079-11

Standards/regulations	IEC/EN 60079-11
Rated insulation voltage	375 V <sub>PP</sub>

#### Electrical isolation Input 1 / input 2

Test voltage	350 V (50 Hz, 60 s)
--------------	---------------------

#### Supply

Supply voltage range	loop-powered, no external supply necessary
Power dissipation	≤ 0.4 W

### Input data

#### Control

Description of the input	Control input, not intrinsically safe
Voltage input signal	12 V ... 31.2 V (Switching signal)
Current consumption	< 25 mA (12 V)
	< 17 mA (24 V ... 31.2 V)

### Output data

#### Switching: Relay

Output description	intrinsically safe
Contact switching type	1 changeover contact per channel
Minimum switching voltage	1 V (1 mA)
Maximum switching voltage	45 V DC (0.25 A)
	30 V DC (4 A)
	45 V AC (4 A, cos φ >0.7)
Typical response time	≤ 10 ms
Typical turn-off time	≤ 10 ms
Switching frequency	≤ 15 Hz

# MACX MCR-EX-AP-2REL-2DI-LP-SP - Relay module



1292332

<https://www.phoenixcontact.com/us/products/1292332>

## Connection data

Connection method	Push-in connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Ex data

Ex installation (EPL)	Gc
Ex i circuits (EPL)	[Ga]
	[Da]
	[Ma]

## Safety data

Input voltage $U_i$	45 V AC
Input current $I_i$	4 A
Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Safety-related maximum voltage $U_m$	253 V AC

## Safety data

Input voltage $U_i$	45 V DC
Input current $I_i$	0.25 A
Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Safety-related maximum voltage $U_m$	253 V AC

## Safety data

Input voltage $U_i$	30 V DC
Input current $I_i$	4 A
Max. internal inductance $L_i$	negligible
Max. internal capacitance $C_i$	negligible
Safety-related maximum voltage $U_m$	253 V AC

## Dimensions

Dimensional drawing	
Width	17.5 mm
Height	107.8 mm
Depth	113.7 mm

1292332

<https://www.phoenixcontact.com/us/products/1292332>

Depth NS 35/7,5	114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)
-----------------	--

## Material specifications

Flammability rating according to UL 94	V0
Housing material	PA 6.6

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20 (Terminal blocks) IP30 (Housing)
Ambient temperature (operation)	-20 °C ... 70 °C (Stand-alone device: any mounting position) -20 °C ... 70 °C (Group assembly: vertical DIN rail without circulating air) -20 °C ... 70 °C (Group assembly: vertical DIN rail with circulating air) -20 °C ... 70 °C (Group assembly: horizontal DIN rail without circulating air) -20 °C ... 70 °C (Group assembly: horizontal DIN rail with circulating air)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	≤ 95 % (non-condensing)

## Approvals

### ATEX

Identification	⊕ II (1) G [Ex ia Ga] IIC
	⊕ II (1) D [Ex ia Da] IIIC
	⊕ II 3(1) G Ex ec nC [ia Ga] IIC T4 Gc
	⊕ I (M1) [Ex ia Ma] I

### IECEX

Identification	[Ex ia Ga] IIC
	[Ex ia Da] IIIC
	Ex ec nC [ia Ga] IIC T4 Gc
	[Ex ia Ma] I

### Safety Integrity Level (SIL, IEC 61508)

Identification	2
----------------	---

## EMC data

Electromagnetic compatibility	Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21
-------------------------------	---

## Standards and regulations

Electrical isolation	4-way isolation
----------------------	-----------------

# MACX MCR-EX-AP-2REL-2DI-LP-SP - Relay module



1292332

<https://www.phoenixcontact.com/us/products/1292332>

## Mounting

Mounting type	NS 35/15, NS 35/7,5
Mounting position	vertical, horizontal

# MACX MCR-EX-AP-2REL-2DI-LP-SP - Relay module




1292332

<https://www.phoenixcontact.com/us/products/1292332>

## Drawings

Dimensional drawing




# MACX MCR-EX-AP-2REL-2DI-LP-SP - Relay module



1292332

<https://www.phoenixcontact.com/us/products/1292332>

Block diagram



1292332

<https://www.phoenixcontact.com/us/products/1292332>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1292332>

### Functional Safety

Approval ID: 22/05-248 R032 V1R0



### IECEx

Approval ID: IECEx BVS 21.0058X



### ATEX

Approval ID: BVS 21 ATEX E 053X

1292332

<https://www.phoenixcontact.com/us/products/1292332>

## Classifications

### ECLASS

ECLASS-13.0	27210192
ECLASS-15.0	27210192

### ETIM

ETIM 10.0	EC002498
-----------	----------

### UNSPSC

UNSPSC 21.0	39121000
-------------	----------

1292332

<https://www.phoenixcontact.com/us/products/1292332>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5ff5c119-b7d2-4106-b119-6497de84f9c1

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)