CRIMPFOX-TC HC 4 - Crimping pliers

1297083

https://www.phoenixcontact.com/us/products/1297083

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for CK 1,6-ED..., CK 2,5-ED..., CK 4,0-ED... turned contacts, 4 marked die stations, unlockable pressure lock, lateral entry, incl. positioning tool

Your advantages

- Marked die stations for precise processing of corresponding cross sections
- Rotating positioning aid ensures precise contact positioning in the crimping area

Commercial data

Item number	1297083
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3135
GTIN	4063151533458
Weight per piece (including packing)	729.8 g
Weight per piece (excluding packing)	729.8 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Notes

Note on application	For 0.14 mm² ... 4.0 mm² solid crimp contacts from the CK1.6 ED..., CK2.5 ED..., CK4.0 ED... series, the packing slip includes a detailed list of the crimp contacts

Product properties

Product type	Crimping tool
Compression	Square crimp
Product property	Marked die stations
	Including positioning guide

Crimping position 1

Min. cross section	0.14 mm²
Max. cross section	1 mm²
AWG min	26
AWG max	18

Crimping position 2

Max. cross section	1.5 mm²
AWG max	16

Crimping position 3

Max. cross section	2.5 mm²
AWG max	14

Crimping position 4

Max. cross section	4 mm²
AWG max	12

Connection data

Conductor connection

Cross section range, metric	0.14 mm² ... 4 mm²
Cross section range AWG	26 ... 12

Dimensions

Width	25 mm
Height	68 mm
Length	256 mm

Material specifications

Color	black (RAL 9005)
Material	Steel

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com