

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety controller (SPS), PLCnext Control; Programming: High-level language and IEC 61131-3; Operating system: Yocto/Linux® (real-time); Programming tool: PLCnext Engineer, Eclipse®, Visual Studio®, MATLAB®/ Simulink®; Processor: Intel® Core™ i7-10700TE, 8x 2 GHz (Standard).

Product description

The BPC 9102S is the most performant Remote Field Controller based on PLCnext Technology. It is also possible to use applications with the highest safety requirements in accordance with SIL 3 or PLe. Standard and safety programming in only one engineering tool, thanks to PLCnext Engineer.

Your advantages

- Real-time-capable Linux operating system for deterministic and reliable execution of time-critical processes
- Supports numerous protocols such as: HTTP, HTTPS, FTP, OPC UA, SNTP, SNMP, SMTP, SQL, MySQL, DCP, etc. – for smooth communication with IT systems
- Direct connection to the Proficloud, the PLCnext Store and any cloud platforms – for seamless IoT integration of your applications
- Support for numerous fieldbus protocols (PROFINET, Modbus TCP/RTU, Ethernet/IP, etc.) for easy integration into existing automation technology systems and installations
- Maximum design freedom thanks to the combination of classic PLC programming with modern high-level languages such as C++, C#, or Python
- Meets the highest security requirements of industrial automation – for the protection of your applications and data

Commercial data

Item number	1246285
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR12
Product key	DRBAAA
GTIN	4063151346836
Weight per piece (including packing)	6,700 g
Weight per piece (excluding packing)	4,772 g
Customs tariff number	85371091
Country of origin	TW

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Controller
Product family	PLCnext Control
Type	Stand-alone

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

System properties

Trusted Platform Module	fTPM 1.2 (Encryption Technology not Chinese)
Retentive data storage	4 Mbyte
RAM	16384 Mbyte DDR4-2400

IEC 61131 runtime system

Program memory	32 Mbyte
Data storage system	64 Mbyte

PROFINET

Device function	PROFINET controller, PROFINET device
Update rate	min. 1 ms
Conformance Class	B
Number of supported devices	max. 256

Function

Safety function	yes
-----------------	-----

Functionality

Programming languages supported	Instruction list (IL)
	Symbolic flowchart (SFC)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python®
	Simulink®

System requirements

Application interface	OPC UA®
-----------------------	---------

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Electrical properties

Power consumption	typ. 50 W
	max. 55 W
Maximum power dissipation for nominal condition	max. 55 W

Supply

Supply voltage (DC)	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including ripple (3.6 V _{PP}))
Power supply connection	Screw terminal blocks, plug-in
Max. current consumption	2.3 A
Typical current consumption	2.1 A

Real-time clock

Realtime clock	Integrated (battery backup)
----------------	-----------------------------

Connection data

COMBICON connector

Conductor cross-section, rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Interfaces

Web server	yes
------------	-----

USB

Number of interfaces	1
Connection method	USB type A, male connector

Ethernet

Bus system	RJ45
Number of interfaces	3
Connection method	RJ45 jack
Transmission speed	1000/2000 Mbps (1000 Mbps (LAN 2 and LAN 3), 1000/2000 Mbps (LAN 1))

Dimensions

External dimensions

Width / Height / Depth	218 mm / 250 mm / 135 mm (without fan module)
	218 mm / 285 mm / 135 mm (With fan module)

Characteristics

Safety data: EN ISO 13849

Performance level (PL)	max. e
------------------------	--------

Safety data: IEC 61508 - High demand

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Safety Integrity Level (SIL)	max. 3
------------------------------	--------

Safety data: EN IEC 62061

Safety Integrity Level Claim Limit (SIL CL)	max. 3
---	--------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C up to 2000 m above mean sea level 0 °C ... 55 °C 2000 m ... 3000 m above mean sea level 0 °C ... 50 °C 3000 m ... 4000 m above mean sea level
Ambient temperature (storage/transport)	-30 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	15g (according to IEC 61131-2)
Shock (storage/transport)	20g (in accordance with EN 60068-2-27/IEC 60068-2-27)
Vibration (operation)	3g (10 Hz ... 55 Hz) (in accordance with EN 60068-2-6/IEC 60068-2-6)
Vibration (storage/transport)	3g (in accordance with EN 60068-2-6/IEC 60068-2-6)
Air pressure (operation)	60 kPa ... 108 kPa (up to 4000 m above mean sea level)
Air pressure (storage/transport)	58 kPa ... 108 kPa (up to 4500 m above mean sea level)

Mounting

Mounting type	Panel mounting
---------------	----------------

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1246285>

PROFINET

Approval ID: Z13531

PROFIsafe

Approval ID: Z20291

PROFINET

Approval ID: Z13532



cULus Listed

Approval ID: E238705

PROFIsafe

Approval ID: Z20354

Cybersecurity Certificate

Approval ID: 968 CSP 1037.00 25



Functional Safety

Approval ID: 01/205/5649.01/23

FS Thermoprocess

Approval ID: 968 INS 799.01 25

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Classifications

ECLASS

ECLASS-13.0	27242207
ECLASS-15.0	27242207
ECLASS-15.0 ASSET	27250101

UNSPSC

UNSPSC 21.0	32151700
-------------	----------

BPC 9102S - Safety controller



1246285

<https://www.phoenixcontact.com/us/products/1246285>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-15
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	4,4'-isopropylidenediphenol(CAS: 80-05-7)
	Lead(CAS: 7439-92-1)
SCIP	7ffeb066-39aa-4355-a5e8-4f354a29e242

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com