

SACC-CIP-M12MSD-4P SMD SH R32X - Contact carrier



1308216

<https://www.phoenixcontact.com/us/products/1308216>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet/PROFINET CAT5 (100 Mbps), 4-position, Pin, straight, M12, D-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

Commercial data

Item number	1308216
Packing unit	100 pc
Minimum order quantity	100 pc
Product key	ABQBGB
GTIN	4063151689414
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	3.373 g
Country of origin	DE

SACC-CIP-M12MSD-4P SMD SH R32X - Contact carrier



1308216

<https://www.phoenixcontact.com/us/products/1308216>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Signal
Number of positions	4
Seal present	yes
Shielded	yes
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Rated surge voltage	2.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A
Transmission speed	100 Mbps
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

Connection data

Connection method	SMD reflow
-------------------	------------

Interfaces

Signal type/category	Ethernet/PROFINET CAT5, 100 Mbps
----------------------	----------------------------------

Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

Connector

SACC-CIP-M12MSD-4P SMD SH R32X - Contact carrier



1308216

<https://www.phoenixcontact.com/us/products/1308216>

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	D

Cable/line

Signal type/category	Ethernet/PROFINET CAT5, 100 Mbps
----------------------	----------------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-40 °C ... 105 °C (Plug / socket) -55 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad


SACC-CIP-M12MSD-4P SMD SH R32X - Contact carrier

1308216

<https://www.phoenixcontact.com/us/products/1308216>

Drawings

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side

SACC-CIP-M12MSD-4P SMD SH R32X - Contact carrier



1308216

<https://www.phoenixcontact.com/us/products/1308216>

Classifications

ETIM

ETIM 9.0

EC002635

SACC-CIP-M12MSD-4P SMD SH R32X - Contact carrier



1308216

<https://www.phoenixcontact.com/us/products/1308216>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com