

NBC-MRDC3/ 2,0-93C/R4AC - Network cable



1308222

<https://www.phoenixcontact.com/us/products/1308222>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, PROFINET, 4-position, shielded, Plug angled M12, coding: D, on Plug straight RJ45, cable length: 2 m

Commercial data

Item number	1308222
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Product key	AF1CJN
GTIN	4063151559069
Weight per piece (including packing)	162.3 g
Weight per piece (excluding packing)	162.3 g
Country of origin	PL

NBC-MRDC3/ 2,0-93C/R4AC - Network cable



1308222

<https://www.phoenixcontact.com/us/products/1308222>

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	4
Shielded	yes

Interfaces

Signal type/category	PROFINET
----------------------	----------

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	1 A

Connector

Connection 2

Type	Plug straight RJ45
------	--------------------

Cable/line

Cable length	2 m
Signal type/category	PROFINET

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
	IP20

NBC-MRDC3/ 2,0-93C/R4AC - Network cable




1308222

<https://www.phoenixcontact.com/us/products/1308222>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1308222>

 cUL Listed Approval ID: File E335024				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	0.5 A	-	-

NBC-MRDC3/ 2,0-93C/R4AC - Network cable



1308222

<https://www.phoenixcontact.com/us/products/1308222>

Classifications

ECLASS

ECLASS-13.0	27060307
ECLASS-15.0	27060307

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

NBC-MRDC3/ 2,0-93C/R4AC - Network cable



1308222

<https://www.phoenixcontact.com/us/products/1308222>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com