

ECOR-1-BSC2/FO/1X21 - Relay base



1308331

<https://www.phoenixcontact.com/us/products/1308331>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

ECOR-1 relay base, for FASTON relay, Fork-type cable lug, 1 changeover contact



Commercial data

Item number	1308331
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C460
Product key	DKF312
GTIN	4063151559410
Weight per piece (including packing)	26.93 g
Weight per piece (excluding packing)	26.57 g
Customs tariff number	85366990
Country of origin	CN

Technical data

Notes

Notes on operation	Do not use to separate SELV / PELV circuits from other circuits, because safe isolation is not guaranteed.
Notes on operation	The system installer must ensure the touch protection of the product (at voltages > 25 V AC/60 V DC). The product is a built-in device without protection against direct contact.
Notes on operation	Basic insulation is maintained against adjacent modules in the DIN rail direction. If the application has higher requirements for the insulation (reinforced insulation), then these must be realized by means of suitable measures (e.g., partition plates).
Notes on operation	Any unused screw connections have to be tightened with torque.

Product properties

Product type	Relay socket
Product family	ESSENTIAL edition

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Basic insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal current I_N	max. 12 A (Depends on application/assembly)
Test voltage (Winding/contact)	4 kV _{rms} (50 Hz, 1 min., winding/contact)
Test voltage (open contact)	1 kV _{rms} (50 Hz, 1 min., open contact)

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V AC
Rated surge voltage	2.5 kV

Connection data

Connection method	Fork-type cable lug
Stripping length	7 mm
Screw thread	M3
Conductor cross-section rigid	0.4 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.4 mm ² ... 1.5 mm ²
Conductor cross-section AWG	21 ... 16
Tightening torque	0.5 Nm ... 1 Nm

Dimensions

Item dimensions

Width	15.7 mm
Height	71 mm
Depth	35.6 mm

ECOR-1-BSC2/FO/1X21 - Relay base



1308331

<https://www.phoenixcontact.com/us/products/1308331>

Material specifications

Color	traffic gray B (RAL 7043)
-------	---------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations

Standards/regulations	IEC 60664-1
-----------------------	-------------

Air clearances and creepage distances between the power circuits

Standards/regulations	IEC 60664-1
-----------------------	-------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

ECOR-1-BSC2/FO/1X21 - Relay base



1308331

<https://www.phoenixcontact.com/us/products/1308331>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1308331>



cUL Recognized
Approval ID: FILE E 113228



UL Recognized
Approval ID: FILE E 113228

ECOR-1-BSC2/FO/1X21 - Relay base



1308331

<https://www.phoenixcontact.com/us/products/1308331>

Classifications

ECLASS

ECLASS-13.0	27371603
ECLASS-15.0	27371603

ETIM

ETIM 10.0	EC001456
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

ECOR-1-BSC2/FO/1X21 - Relay base



1308331

<https://www.phoenixcontact.com/us/products/1308331>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.293 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com