

RCK-TGUM/BL12/10,0PUR-UX - Master cable



1260769

<https://www.phoenixcontact.com/us/products/1260769>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Master cable, application: Sensor/actuator box, number of positions: 12, slot assignment: single, status display: no; master cable connection: M23 plug connection, PUR/PVC, cable length: 10 m, shielding: no, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %). This product is in the process of being discontinued. This product must no longer be considered for new projects. Please contact your sales representative for alternatives.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1260769 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB34 |
| Product key | ABRDCA |
| GTIN | 4063151414610 |
| Weight per piece (including packing) | 1,142 g |
| Weight per piece (excluding packing) | 1,128.824 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

1260769

<https://www.phoenixcontact.com/us/products/1260769>

Technical data

Notes

| | |
|--------------------|--|
| Notes on operation | The master cable is earmarked for use on the sensor/actuator boxes with an M23 plug-in connection. |
|--------------------|--|

Product properties

| | |
|---------------------|-------------------------|
| Product type | Master cable, assembled |
| Application | Sensor/actuator box |
| Number of positions | 12 |

Electrical properties

| | |
|-----------------------|---------|
| Nominal voltage U_N | 48 V AC |
| | 60 V DC |

Connection data

| | |
|-------------------|------------------|
| Connection method | Fixed connection |
|-------------------|------------------|

Signaling

| | |
|------------------------|----|
| Status display present | no |
|------------------------|----|

Material specifications

| | |
|--|-------------|
| Material Housing | PUR |
| Material of contact, master cable side | CU alloy |
| Material of the contact carrier on the master cable side | PA |
| Material of contact surface, master cable side | gold-plated |

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M23 |

Connection 2

| | |
|-------------|----------------|
| Head design | free cable end |
|-------------|----------------|

Cable/line

| | |
|--------------|------|
| Cable length | 10 m |
|--------------|------|


PUR/PVC black [PUR]

RCK-TGUM/BL12/10,0PUR-UX - Master cable



1260769

<https://www.phoenixcontact.com/us/products/1260769>

| | |
|---|--|
| Dimensional drawing |  |
| Cable weight | 107.4 kg/km |
| UL AWM Style | 20549 (80°C/300 V) |
| Number of positions | 11 |
| Shielded | no |
| Cable type | PUR/PVC black [PUR] |
| Conductor structure signal line | 19x 0.15 mm |
| AWG signal line | 22 |
| Conductor structure, voltage supply | 42x 0.15 mm |
| AWG power supply | 18 |
| Conductor cross-section | 8x 0.34 mm ² (Signal line) 3x 0.75 mm ² (power line) |
| Wire diameter incl. insulation | 1.3 mm ±0.1 mm (Signal line) 1.8 mm ±0.1 mm (power line) |
| External cable diameter | 8.50 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | black RAL 9005 |
| Conductor material | Bare Cu litz wires |
| Material wire insulation | PVC |
| Single wire, color | brown, blue, green/yellow, white, green, yellow, gray, pink, red, black, violet |
| Inner sheath thickness | ≥ 0.15 mm |
| Thickness, outer sheath | ≥ 0.38 mm |
| Overall twist | Wires twisted in layers |
| Max. conductor resistance | ≤ 53 Ω/km (Signal line) ≤ 26 Ω/km (power line) |
| Insulation resistance | ≥ 5 MΩ*km |
| Nominal voltage, cable | 300 V AC |
| Test voltage Core/Core | 2000 V (50 Hz, 5 min.) |
| Minimum bending radius, fixed installation | 7.5 x D |
| Minimum bending radius, flexible installation | 10 x D |
| Smallest bending radius, fixed installation | 64 mm |
| Smallest bending radius, movable installation | 85 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 1500000, Bending radius: 10 x D, Traversing path: 2 m, Traversing rate: 2 m/s |
| Flame resistance | DIN EN 50265 |
| Resistance to oil | according to VDE 0472 Part 803 |

RCK-TGUM/BL12/10,0PUR-UX - Master cable



1260769

<https://www.phoenixcontact.com/us/products/1260769>

| | |
|---------------------------------|--|
| Other resistance | Highly resistant to acids, alkaline solutions and solvents |
| Special properties | Silicone-free |
| Ambient temperature (operation) | -40 °C ... 90 °C (cable, fixed installation) |
| | -5 °C ... 80 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-----------------------------------|
| Degree of protection | IP65 |
| | IP67 |
| Ambient temperature (operation) | -40 °C ... 125 °C (Plug / socket) |

Drawings

Schematic diagram



Pin assignment M23 socket, 12-pos., female side view

RCK-TGUM/BL12/10,0PUR-UX - Master cable



1260769

<https://www.phoenixcontact.com/us/products/1260769>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1260769>



EAC

Approval ID: 19060508

RCK-TGUM/BL12/10,0PUR-UX - Master cable



1260769

<https://www.phoenixcontact.com/us/products/1260769>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

RCK-TGUM/BL12/10,0PUR-UX - Master cable



1260769

<https://www.phoenixcontact.com/us/products/1260769>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com