

FPM 17.3 69K - Monitor

1261657

<https://www.phoenixcontact.com/us/products/1261657>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Similar figure

Hygiene monitor with 43.9 cm/17.3" TFT display (capacitive multi-touchscreen), 1920 x 1080 pixels (Full HD) in all-around closed stainless-steel housing without screws or sharp edges.

Your advantages

- Robust and high-performance under extreme conditions
- Stable and resistant with a closed stainless-steel housing
- Hygienic design with passive cooling
- Easy mounting with boom adapter or VESA adapter
- Capacitive multi-touch display for convenient multi-finger operation with gloves

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1261657 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DR12 |
| Product key | DRBBAD |
| GTIN | 4063151369255 |
| Weight per piece (including packing) | 6 g |
| Weight per piece (excluding packing) | 4.6 g |
| Customs tariff number | 85285210 |
| Country of origin | DE |

Technical data

Notes

| | |
|--------------------|-------------------------------------------------------------------------------------------|
| Order information: | Please note that an adapter listed under "Accessories" is required to operate the device. |
|--------------------|-------------------------------------------------------------------------------------------|

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Product properties

| | |
|--------------|---------|
| Product type | Monitor |
|--------------|---------|

Computer data

| | |
|---------------------|--------------------------|
| Processor | without processor |
| Operating system | without operating system |
| RAM | without RAM |
| Data storage system | without data storage |
| Cooling | passive |
| Slots | without slots |
| Extras | without |

Display

| | |
|-----------------------|--------------------------------|
| Display type | 43.9 cm / 17.3"-TFT |
| Screen resolution | 1920 x 1080 Pixel(s) (Full HD) |
| Touch technology | projective-capacitive (PCAP) |
| Display lighting type | LED |
| Brightness | 250 cd/m ² |
| MTBF | 50000 h |
| Color spectrum | 16.2 million colors |
| Reading angle left | 89.00 ° |
| Reading angle right | 89.00 ° |
| Reading angle top | 89.00 ° |
| Reading angle bottom | 89.00 ° |

System properties

| | |
|---------------|-----------------------|
| User software | without user software |
|---------------|-----------------------|

Electrical properties

Supply

| | |
|----------------------|---------------------|
| Supply voltage | 24 V DC |
| Supply voltage range | 18 V DC ... 30 V DC |

Interfaces

| | |
|------------|---------------|
| Interfaces | 3x USB 2.0 |
| | 1x USB server |

1261657

<https://www.phoenixcontact.com/us/products/1261657>

| | |
|---------------------|----------------------------|
| Optional interfaces | Without optional interface |
| Monitor output | 1x DisplayPort |
| | 1x HDMI |
| Network | without network |
| Bus system | without bus system |

Dimensions

External dimensions

| | |
|------------------------|-------------------------|
| Width / Height / Depth | 431 mm / 261 mm / 68 mm |
|------------------------|-------------------------|

Material specifications

| | |
|----------------------|-------------------------------------------|
| Material front plate | Glass (3 mm), hardened and non-reflective |
| Housing material | Stainless steel, fully enclosed |

Environmental and real-life conditions

Ambient conditions

| | |
|------------------------------------------|--------------------------------|
| Degree of protection | IP69K |
| Ambient temperature (operation) | 0 °C ... 50 °C |
| Permissible humidity (operation) | 10 % ... 85 % (non-condensing) |
| Permissible humidity (storage/transport) | 10 % ... 85 % (non-condensing) |
| Shock | DIN EN 60068-2-27 |
| Vibration (operation) | DIN EN 60068-2-6 |

Mounting

| | |
|---------------|-----------------------------|
| Mounting type | VESA holder (via adapter) |
| | Tube mounting (via adapter) |
| Holder system | VESA MIS-D 100 C |

FPM 17.3 69K - Monitor



1261657

<https://www.phoenixcontact.com/us/products/1261657>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19200201 |
| ECLASS-15.0 | 19200201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC004862 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43211900 |
|-------------|----------|

FPM 17.3 69K - Monitor



1261657

<https://www.phoenixcontact.com/us/products/1261657>

Environmental product compliance

EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com