

PRC 20/5-C1-FC-FS2,5 6-14 - Coupler connector



1308661

<https://www.phoenixcontact.com/us/products/1308661>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Coupler connector, Range of articles: PRC 20, color: black/red, number of positions: 5, min. conductor cross-section: 0.5 mm², max. conductor cross-section: 2.5 mm², rated voltage: 400 V, rated current: 20 A, Connection method: Screw connection, min. cable diameter: 8 mm, max. cable diameter: 14 mm, For assembly notes, please refer to the packing slip, scope: AC

Your advantages

- More space on the device front with current transmission up to 20 A in a minimum amount of space
- Duo-Unlock technology for greater flexibility during installation and maintenance
- Reliable use under extreme ambient conditions with high degrees of protection and impact resistance
- Simple handling with proven crimp or screw connection technology
- Mechanical and color coding for quick and error-free startup

Commercial data

Item number	1308661
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB03
Product key	ABLHBA
GTIN	4063151559724
Weight per piece (including packing)	60.8 g
Weight per piece (excluding packing)	49.381 g
Customs tariff number	85366990
Country of origin	PL

PRC 20/5-C1-FC-FS2,5 6-14 - Coupler connector



1308661

<https://www.phoenixcontact.com/us/products/1308661>

Technical data

Notes

Note on application	For assembly notes, please refer to the packing slip
---------------------	--

Product properties

Product type	Installation connector
Product family	PRC 20
Area of application	AC
Number of positions	5
Connection profile	4+PE
Coding	5-C1

Insulation characteristics

Protection class	II (plastic housing)
------------------	----------------------

Electrical properties

Rated voltage	400 V (III/2.00) in accordance with IEC 61984
	400 V AC (III/2.00) in accordance with IEC 61535
	600 V AC / DC (III/2.00) in accordance with UL 2238 / UL 2237
	500 V DC (III/2.00) in accordance with IEC 61535
Rated current	20 A (With 2.5 mm ² conductor cross-section in accordance with IEC 61984)
	20 A (With 2.5 mm ² conductor cross-section in accordance with IEC 61535)
	20 A (With 2.5 mm ² /AWG 14, in accordance with UL 2238)
	20 A (With 2.5 mm ² /AWG 14, in accordance with UL 2237)

Dimensions

Width	28.5 mm
Height	28.5 mm
Length	80.4 mm

Material specifications

Color (Housing)	black (RAL 9005)
Material Housing	PPE
Material Contact carrier	PPE
Material Contact	CuZn (Contact material, Pb < 0.1)
Material Cable gland	PC
Material Seal	EPDM (Cable seal)
	EPDM (Housing seal)
Flammability rating according to UL 94	V0

Cable/line

External cable diameter	8 mm ... 14 mm
-------------------------	----------------

PRC 20/5-C1-FC-FS2,5 6-14 - Coupler connector



1308661

<https://www.phoenixcontact.com/us/products/1308661>

Single wire, cross section	0.5 mm ² 2.5 mm ²
Stripping length of the individual wire	10 mm (Lay PE conductor 8 mm leading)
Halogen-free	yes (in accordance with IEC 61249-2-21:2003- 11 Cl.3.1)

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	500 (Test specification: IEC 60512-13-2)
-----------------------------	--

Environmental and real-life conditions

Ambient conditions


Degree of protection	IP66
	IP68 (2 m / 2 h)
	IP69
Category of shock impact	IK08 (-25°C)
Ambient temperature (operation)	-40 °C ... 85 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Ambient temperature (assembly)	-5 °C ... 85 °C

Standards and regulations

Standards/specifications	IEC 61984:2008
	IEC 61535:2019
	UL 2238
	UL 2237

Drawings


Diagram



PRC 20/5...
IEC 60512-5-2 / 4 conductors

Derating

Diagram



PRC 20/5...
IEC 61535 / 3 conductors

Derating

PRC 20/5-C1-FC-FS2,5 6-14 - Coupler connector



1308661

<https://www.phoenixcontact.com/us/products/1308661>

Classifications

ECLASS

ECLASS-13.0	27440605
ECLASS-15.0	27440605

ETIM

ETIM 10.0	EC002560
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PRC 20/5-C1-FC-FS2,5 6-14 - Coupler connector



1308661

<https://www.phoenixcontact.com/us/products/1308661>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)
SCIP	9fd7364b-a114-4c99-8252-74641e832599

EF3.1 Climate Change

CO2e kg	1.118 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com