

# EV-RCM-6DC-WAT-X10 - Differential current monitoring

1309695

<https://www.phoenixcontact.com/us/products/1309695>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX control modular, the residual current monitoring module is used for AC and DC residual current detection in AC charging points. The higher-level safety equipment (e.g., residual current device) is protected against potential DC residual currents.

## Commercial data

Item number	1309695
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	EM01
Product key	XWBRYA
GTIN	4063151560867
Weight per piece (including packing)	46.4 g
Weight per piece (excluding packing)	46.4 g
Customs tariff number	85437090
Country of origin	PL

# EV-RCM-6DC-WAT-X10 - Differential current monitoring



1309695

<https://www.phoenixcontact.com/us/products/1309695>

## Technical data

### Product properties

Product type	Residual current monitoring module
Product family	CHARX control modular
Type	1-channel
Charging standard	Type 2
Charging mode	Mode 3
Number of charging points	1

### Electrical properties

Type of charging current	AC
--------------------------	----

#### Measuring range: Residual current

Residual current $I_{\Delta n}$	30 mA (AC)
	6 mA (DC)
Rated current $I_n$	100 A (1-phase)
	40 A (3-phase)

#### Supply

Supply voltage range	10.8 V DC ... 13.2 V DC (nominal voltage range)
Nominal power consumption	min. 60 mW
Frequency range	50 Hz ... 60 Hz

### Connection data

#### Conductor connection

Conductor cross-section AWG	26
-----------------------------	----

### Interfaces

Number of interfaces	2 (Error/Test)
----------------------	----------------

### Dimensions

#### RCM

Width	60.7 mm
Height	33.6 mm
Depth	32.5 mm

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C

### Standards and regulations

# EV-RCM-6DC-WAT-X10 - Differential current monitoring



1309695

<https://www.phoenixcontact.com/us/products/1309695>

## Standards

Standards/regulations

IEC 62955

## Mounting

Mounting position

any

# EV-RCM-6DC-WAT-X10 - Differential current monitoring



1309695

<https://www.phoenixcontact.com/us/products/1309695>

## Classifications

### ECLASS

ECLASS-13.0	27144703
ECLASS-15.0	27144703

### ETIM

ETIM 10.0	EC002889
-----------	----------

### UNSPSC

UNSPSC 21.0	39121800
-------------	----------

# EV-RCM-6DC-WAT-X10 - Differential current monitoring



1309695

<https://www.phoenixcontact.com/us/products/1309695>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)