

SACC-CIP-M8FS-3P SMD SH R32PD - Contact carrier



1311885

<https://www.phoenixcontact.com/us/products/1311885>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Contact carrier, 3-position, Socket, straight, M8, A-coding, SMD reflow



The figure shows standard version

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Additional gasket for the device when not plugged in

Commercial data

Item number	1311885
Packing unit	120 pc
Minimum order quantity	120 pc
Product key	ABQHCB
GTIN	4063151563134
Weight per piece (including packing)	5.07 g
Weight per piece (excluding packing)	2.211 g
Country of origin	DE

1311885

<https://www.phoenixcontact.com/us/products/1311885>

Technical data

Product properties

Product type	Contact insert
Number of positions	3
Shielded	yes
Coding	A
Thread type	M8

Insulation characteristics

Overvoltage category	III
----------------------	-----

Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	3 A

Connection data

Connection method	SMD reflow
-------------------	------------

Signaling

Status display	no
Status display present	no

Material specifications

Material Insulating body	PA
Material Contact	CuZn
Material Contact surface	Au
Material Seal	FKM
Flammability rating according to UL 94	V0

Connector

Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

1311885

<https://www.phoenixcontact.com/us/products/1311885>

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
Ambient temperature (operation) (male connector/female connector)	-25 °C ... 105 °C
	-40 °C ... 105 °C (without mechanical actuation)

Standards and regulations


Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad

Drawings

Schematic diagram



Pin assignment M8 socket, 3-pos., view female side

SACC-CIP-M8FS-3P SMD SH R32PD - Contact carrier



1311885

<https://www.phoenixcontact.com/us/products/1311885>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1311885>

 cULus Recognized Approval ID: E221474-20160506				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	60 V	4 A	-	-

1311885

<https://www.phoenixcontact.com/us/products/1311885>

Classifications

ECLASS

ECLASS-13.0	27440223
ECLASS-15.0	27440223

ETIM

ETIM 10.0	EC003557
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1311885

<https://www.phoenixcontact.com/us/products/1311885>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com