

# CUC-IND-J1ST-A/R4LS-LED-PG-S - Modular RJ45 PCB connectors



1321246

<https://www.phoenixcontact.com/us/products/1321246>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 90 °, Tab up, Shielded, shield springs, Bicolor LED (green-yellow, green-yellow), number of positions: 8, 10 Gbps, PoE++, THT-THR, THD, Reflow, IP20, type of packaging: Tape and Reel

## Your advantages

- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- 360° shielding ensures reliable transmission, even in industrial applications
- With integrated hybrid LEDs as optical status indicators of data transmission
- Automated handling process thanks to reflow capability
- The extended temperature range from -40°C to +105°C enables use in demanding industrial applications
- Tape-on-reel packaging

## Commercial data

Item number	1321246
Packing unit	84 pc
Minimum order quantity	84 pc
Sales key	AB12
Product key	ABNADA
GTIN	4063151608309
Weight per piece (including packing)	9.34 g
Weight per piece (excluding packing)	9.3 g
Customs tariff number	85366930
Country of origin	CN

# CUC-IND-J1ST-A/R4LS-LED-PG-S - Modular RJ45 PCB connectors



1321246

<https://www.phoenixcontact.com/us/products/1321246>

## Technical data

### Product properties

Slots	1x1 single-port
Orientation to PCB	90.00 °
Type	THD
Number of positions	8 (8P8C)
Type of locking	Snap-in locking, Tab up
Shielding	Shielded, shield springs
Status display	Bicolor LED (green-yellow, green-yellow)
Processing notes	Reflow
Type of packaging	Tape and Reel
Transmission speed	10 Gbps
Power transmission	PoE++ (according to IEEE 802.3bt)
Power PSE	90 W (Class 8 in accordance with IEEE 802.3bt)
Power PD	71 W (Class 4 in accordance with IEEE 802.3bt)

### Electrical properties

Pollution degree	2 (IEC 60664-1)
Overvoltage category	I (IEC 60664-1)
Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC (IEC 60664-1)
Rated current	1.5 A (IEC 60603-7)
Insulation resistance	> 500 MΩ (IEC 60603-7)
Test voltage (Contact/contact)	1.5 kV DC (IEC 60603-7)
Test voltage (Contact/shield)	1.5 kV DC (IEC 60603-7)

### Dimensions

Length	17.1 mm
Width	17 mm
Height	18 mm
Installed height	12.80 mm
Data pin length	2.00 mm

### Material specifications

Material Contact carrier	PA
Flame resistance	UL 94 V0
Halogen-free	yes
Material Housing	Copper alloy
Material Housing coating	Ni
Material Housing pin coating (top layer/selective)	Ni
Material Contact	Copper alloy

# CUC-IND-J1ST-A/R4LS-LED-PG-S - Modular RJ45 PCB connectors



1321246

<https://www.phoenixcontact.com/us/products/1321246>

Material Solder contact coating (intermediate layer)	Ni
Material Solder contact coating (top layer/selective)	Au
Material Plug contact coating (top layer/selective)	Au (1.27 µm/50 µ")
Material Plug contact coating (intermediate layer)	Ni

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 750 (IEC 60603-7)
Insertion force	< 20 N (IEC 60603-7)
Withdrawal force	< 20 N (IEC 60603-7)

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Degree of protection (plugged in)	IP20 (IEC 60603-7)
Degree of protection (Not plugged in)	IP20 (IEC 60603-7)

### Test specification for vibration - sine (IEC 60068-2-6)

Acceleration	200 m/s <sup>2</sup>
Frequency	20 - 2000 Hz
Amplitude	1 mm
Cycles	10 cycles per axis, 20 sweeps
Sweep speed	1 octave/min

### Test specification Shock (IEC 60068-2-27)

Pulse shape	Half-sine
Acceleration	500 m/s <sup>2</sup>

## Mounting

### Processing notes


Mounting type	THT-THR
Moisture Sensitive Level	MSL 2 (IPC/JEDEC J-STD-020)
Solder cycles in the reflow	3 (IPC/JEDEC J-STD-020)

1321246

<https://www.phoenixcontact.com/us/products/1321246>

## Drawings

Diagram



Classification reflow soldering profile

# CUC-IND-J1ST-A/R4LS-LED-PG-S - Modular RJ45 PCB connectors



1321246

<https://www.phoenixcontact.com/us/products/1321246>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1321246>



**cUL Recognized**  
Approval ID: FILE E 335024



**UL Recognized**  
Approval ID: FILE E 335024

# CUC-IND-J1ST-A/R4LS-LED-PG-S - Modular RJ45 PCB connectors



1321246

<https://www.phoenixcontact.com/us/products/1321246>

## Classifications

### ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

### ETIM

ETIM 10.0	EC002637
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# CUC-IND-J1ST-A/R4LS-LED-PG-S - Modular RJ45 PCB connectors



1321246

<https://www.phoenixcontact.com/us/products/1321246>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6b185eef-775f-41da-9960-2b08ae905712

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)