

# ME MAX 45 G 3-3 BK - Electronics housing



1326233  
<https://www.phoenixcontact.com/us/products/1326233>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail housing, Complete housing with metal foot catch, tall design, without vents, width: 45.2 mm, height: 99 mm, depth: 113.65 mm, color: light gray (similar RAL 7035), cross connection: DIN rail bus connector (optional), number of positions cross connector: 5

## Your advantages

- Easy installation
- Available in overall widths from 6.2 mm ... 90 mm, modular extension possible
- Variety of connection technology
- Can be mounted on the DIN rail
- With DIN-rail-mountable bus connector and power connector system as an option
- Transparent front cover can be swiveled

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1326233                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 100 pc                         |
| Note                                 | Made to order (non-returnable) |
| Product key                          | ACHABA                         |
| GTIN                                 | 4063151616298                  |
| Weight per piece (including packing) | 88.7 g                         |
| Weight per piece (excluding packing) | 73.552 g                       |
| Country of origin                    | DE                             |

# ME MAX 45 G 3-3 BK - Electronics housing



1326233

<https://www.phoenixcontact.com/us/products/1326233>

## Technical data


### Notes

|                |                                                                       |
|----------------|-----------------------------------------------------------------------|
| Assembly note  | Please observe the application note in the download area.             |
| Recommendation | Material of contact pads for bus connector, galvanic gold (hard gold) |

### Product properties

|                                   |                                                                                   |
|-----------------------------------|-----------------------------------------------------------------------------------|
| Product type                      | Complete housing                                                                  |
| Housing type                      | DIN rail housing                                                                  |
| Housing series                    | ME-MAX                                                                            |
| Product family                    | ME MAX 45..                                                                       |
| Type                              | Lower housing parts without vents, housing cover necessary to complete the module |
| Number of positions               | 36                                                                                |
|                                   | 60                                                                                |
| Max. number of positions          | 60 (pitch: 3.5 mm)                                                                |
|                                   | 48 (pitch: 5 mm)                                                                  |
|                                   | 36 (pitch: 7.25 mm/7.5 mm)                                                        |
| Number of rows                    | 3                                                                                 |
|                                   | 3                                                                                 |
| Number (Connection openings)      | 6                                                                                 |
| Ventilation openings present      | no                                                                                |
| Anzahl der Etagen Housing (Makro) | 3 (Both sides)                                                                    |

### Dimensions

|                                                                                     |           |
|-------------------------------------------------------------------------------------|-----------|
| Dimensional drawing                                                                 |           |
|  |           |
| Width                                                                               | 45.2 mm   |
| Height                                                                              | 99 mm     |
| Depth                                                                               | 113.65 mm |
| Depth from top edge of DIN rail                                                     | 107 mm    |

### PCB design

|               |                   |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

### Material specifications

|                 |                       |
|-----------------|-----------------------|
| Color (Housing) | light gray (RAL 7035) |
|-----------------|-----------------------|

|                                        |     |
|----------------------------------------|-----|
| Flammability rating according to UL 94 | V0  |
| CTI according to IEC 60112             | 600 |
| Housing material                       | PA  |

## Environmental and real-life conditions

### Power dissipation single housing for 20 °C

|                     |          |
|---------------------|----------|
| Ambient temperature | 20 °C    |
| Reduction factor    | 1        |
| Mounting position   | vertical |
| Power dissipation   | 7.6 W    |

### Power dissipation single housing for 30 °C

|                     |          |
|---------------------|----------|
| Ambient temperature | 30 °C    |
| Reduction factor    | 0.91     |
| Mounting position   | vertical |
| Power dissipation   | 6.9 W    |

### Power dissipation single housing for 40 °C

|                     |          |
|---------------------|----------|
| Ambient temperature | 40 °C    |
| Reduction factor    | 0.81     |
| Mounting position   | vertical |
| Power dissipation   | 6.2 W    |

### Power dissipation single housing for 50 °C

|                     |          |
|---------------------|----------|
| Ambient temperature | 50 °C    |
| Reduction factor    | 0.7      |
| Mounting position   | vertical |
| Power dissipation   | 5.3 W    |

### Power dissipation single housing for 60 °C

|                     |          |
|---------------------|----------|
| Ambient temperature | 60 °C    |
| Reduction factor    | 0.57     |
| Mounting position   | vertical |
| Power dissipation   | 4.4 W    |

### Power dissipation single housing for 70 °C

|                     |          |
|---------------------|----------|
| Ambient temperature | 70 °C    |
| Reduction factor    | 0.49     |
| Mounting position   | vertical |
| Power dissipation   | 3.8 W    |

### Vibration test

|               |                             |
|---------------|-----------------------------|
| Specification | IEC 60068-2-6:2007-12       |
| Frequency     | 10 - 150 - 10 Hz            |
| Sweep speed   | 1 octave/min                |
| Amplitude     | 0.15 mm (10 Hz ... 58.1 Hz) |

1326233

<https://www.phoenixcontact.com/us/products/1326233>

|                        |                         |
|------------------------|-------------------------|
| Acceleration           | 2g (58.1 Hz ... 150 Hz) |
| Test duration per axis | 2.5 h                   |
| Test directions        | X-, Y- and Z-axis       |

## Mechanical strength / tumbling barrel

|                |                     |
|----------------|---------------------|
| Specification  | IEC 60998-1:2002-12 |
| Height of fall | 50 cm               |
| Frequency      | 10                  |

## Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Specification                  | IEC 60068-2-27:2008-02            |
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 15g                               |
| Shock duration                 | 11 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |

## Degree of protection (IP code)

|               |                                                   |
|---------------|---------------------------------------------------|
| Specification | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
|---------------|---------------------------------------------------|

## Ambient conditions

|                                         |                                                    |
|-----------------------------------------|----------------------------------------------------|
| Max. IP code to attain                  | IP20                                               |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %                                               |

## PCB data

|                       |                   |
|-----------------------|-------------------|
| Number of PCB holders | 2                 |
| Type of PCB mount     | Latching          |
| Thickness of the PCB  | 1.4 mm ... 1.8 mm |

## Mounting


|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

## Packaging specifications

|                      |                     |
|----------------------|---------------------|
| Type of packaging    | packed in cardboard |
| Outer packaging type | Carton              |

## Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

# ME MAX 45 G 3-3 BK - Electronics housing



1326233

<https://www.phoenixcontact.com/us/products/1326233>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190101 |
| ECLASS-15.0 | 27190101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001031 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# ME MAX 45 G 3-3 BK - Electronics housing



1326233

<https://www.phoenixcontact.com/us/products/1326233>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)