

# PRC 5-SPLK-2,5 - Conductor connector



1274812

<https://www.phoenixcontact.com/us/products/1274812>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor connector, Range of articles: PRC 35, design: Straight, color: black, number of positions: 5, min. conductor cross-section: 0.75 mm<sup>2</sup>, max. conductor cross-section: 4 mm<sup>2</sup>, rated voltage: 1000, rated current: 32 A, Connection method: Screw connection, min. cable diameter: 9.5 mm, max. cable diameter: 12.5 mm

## Your advantages

- Easily extend and repair lines and cables
- Suitable for use outdoors, thanks to UV- and saltwater-resistant plastics
- Patented closure technology prevents the housing from being opened accidentally

## Commercial data

Item number	1274812
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB03
Product key	ABL CZD
GTIN	4063151466978
Weight per piece (including packing)	152.5 g
Weight per piece (excluding packing)	136.619 g
Customs tariff number	85369010
Country of origin	PL

# PRC 5-SPLK-2,5 - Conductor connector



1274812

<https://www.phoenixcontact.com/us/products/1274812>

## Technical data

### Product properties

Product type	Cable connector
Product family	PRC 35
Type	Straight
Number of positions	5

### Insulation characteristics

Protection class	II (double or reinforced insulation)
Degree of pollution	2

### Dimensions

Width	52 mm
Height	52 mm
Length	176 mm

### Connection data

#### Connection technology

Connection method	Screw connection
-------------------	------------------

#### Conductor connection

Tightening torque	1.2 Nm (Contact screw)
	6 Nm (Cable gland)

### Electrical properties

Rated voltage	1000 DIN VDE 60664-1
	600 V AC (III/2.00) In accordance with UL 2238
	500 V DC (III/2.00) in accordance with IEC 61535, when mounted
Rated current	32 A (Derating in accordance with IEC 60512-5-2, 4 mm <sup>2</sup> , four-conductor current feed, max. ambient temperature of 50°C)

### Material specifications

Color (Housing)	black (RAL 9005)
Material Seal	EPDM (Cable seal)
	EPDM (Housing seal)
Material Housing	PPE
Material Contact carrier	PPE
Material Contact	Cu alloy
Flammability rating according to UL 94	V0

### Cable/line

External cable diameter	9.5 mm ... 12.5 mm
External cable diameter	9.5 mm ... 12.5 mm

# PRC 5-SPLK-2,5 - Conductor connector



1274812

<https://www.phoenixcontact.com/us/products/1274812>

Single wire, cross section	0.75 mm <sup>2</sup> 4 mm <sup>2</sup> 18 AWG 12 AWG
Halogen-free	yes (in accordance with IEC 61249-2-21:2003- 11 Cl.3.1)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67 (Test specification: IEC 60529)
Category of shock impact	IK07
Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	5 °C ... 85 °C

# PRC 5-SPLK-2,5 - Conductor connector




1274812

<https://www.phoenixcontact.com/us/products/1274812>

## Drawings

Diagram



Derating

# PRC 5-SPLK-2,5 - Conductor connector



1274812

<https://www.phoenixcontact.com/us/products/1274812>

## Classifications

### ECLASS

ECLASS-15.0	27440691
ECLASS-13.0	27440691

### ETIM

ETIM 10.0	EC002863
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PRC 5-SPLK-2,5 - Conductor connector



1274812

<https://www.phoenixcontact.com/us/products/1274812>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
	Triphenyl phosphate(CAS: 115-86-6)
SCIP	b08b6d57-2286-4bb1-9968-145dc7fd7ee1

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)