

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Combination of relay interface and electronic fuse protection on overall width: 6.2 mm, individual configuration of the nominal current (1 A ... 6 A), adjustable output characteristic, active signal output, easy system integration, with screw connection

Commercial data

Item number	1328357
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C461
Product key	DK622F
GTIN	4063151620974
Weight per piece (including packing)	44.01 g
Weight per piece (excluding packing)	42.81 g
Customs tariff number	85364190
Country of origin	DE

Technical data

Notes

Notes on operation	Repeated hard short circuits can reduce the melting integral of the integrated backup fuse.
Notes on operation	A suitable flyback diode must be used when switching inductive loads
Notes on operation	If the DIP switches are not covered by an adjacent module, the PLC-ATP partition plate must be used for ESD protection
Notes on operation	The device contains components that can be damaged or destroyed by electrostatic discharge. When handling the device, observe the necessary safety precautions against electrostatic discharge (ESD) according to EN 61340-5-1 and EN 61340-5-2.
Notes on operation	The PLC-ATP separating plate should be installed for safe isolation between adjacent modules
Notes on operation	Do not connect adjacent channels to SELV/ PELV and voltages dangerous to the touch.
Notes on operation	At least one functional insulation against adjacent modules is complied with in the support rail direction. If the application has higher requirements on the insulation (basic or reinforced insulation), then these must be realized through suitable measures (e. g., partition plates).
Notes on operation	Do not use to separate SELV / PELV circuits from other circuits, because safe isolation is not guaranteed.

Product properties

Product type	Relay Module
Product family	PLC-INTERFACE
Application	with integrated electronic circuit breaker
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	I
Pollution degree	2

Electrical properties

Maximum power dissipation for nominal condition	< 1.6 W
Fuse	electronic

Input data

Operating voltage (U_N)	24 V DC ($U_{In+} - U_{A2}$)
Operating voltage range (DC)	19.2 V DC ... 30 V DC ($U_{In+} - U_{A2}$)
Current consumption (I_{N+})	12 mA
Tripping current (I_N)	1 A (adjustable)
	2 A (adjustable)
	3 A (adjustable)
	4 A (adjustable)

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

	5 A (adjustable)
	6 A (preset)
Measuring tolerance	± 15 %
Power dissipation	0.06 W (Without load, A1 low)
	0.4 W (Without load, A1 high)
	< 1.6 W (Normal operation)

Switching: Switching input A1

Nominal switch-on voltage	24 V ($U_{A1} - U_{A2}$)
Switch-on voltage range	11 V ... 30 V ($U_{A1} - U_{A2}$)
Switch-off voltage range	0 V ... 2 V ($U_{A1} - U_{A2}$)
Current consumption (I_{A1})	4 mA (24 V)
Switch-on time	36 ms
Switch-off time	10 ms
Switching frequency	≤ 2.5 Hz

Output data

Load circuit: Power MOSFET switching output (positive switching)

Voltage drop	0.16 V (6 A, $U_{In+} - U_{out}$)
Short-circuit switching capacity	100 A DC
	300 A DC (<5 short circuits)
Required backup fuse	Only required if I_{max} of power supply unit > short-circuit switching capacity. Integrated failsafe element
Fail-safe element	15 A
Surge voltage protection	> 33 V
Max. capacitive load	12000 µF (Depending on the current setting and the short-circuit current available)
Shutdown time (in FUSE MODE)	≤ 15 ms (Short circuit ≥3 x I_N)
	0.1 s (Short circuit 2 ... <3 x I_N)
	1 s (Short circuit 1.5 ... <2 x I_N)
	4 s (Short circuit 1.1 ... <1.5 x I_N)
Undervoltage switch-off	≤ 17.8 V (active)
	≥ 19 V (inactive)
Overvoltage switch-off	≥ 30.5 V (active)
	≤ 29.5 V (inactive)
Waiting time	5 s (Between the pulses)
Number	5 (Start attempts in hiccup mode)

Signal: Feedback contact

Output voltage	$U_{In+} - 0.7$ V (high level)
Current (Maximum current)	≤ 20 mA
State condition (Normal operation)	low
State condition (Error)	high (Fuse has blown)
State condition (Hiccup mode)	high (After all 5 start attempts have been completed)

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Connection data

Connection method	Screw connection
Stripping length	8 mm
Conductor cross-section rigid	0.2 mm² ... 2.5 mm²
Conductor cross-section rigid (2 conductors with same cross section)	0.14 mm² ... 1.5 mm²
Conductor cross-section flexible	0.2 mm² ... 2.5 mm²
	0.14 mm² ... 1.5 mm²
Conductor cross-section flexible (2 conductors with same cross section)	0.5 mm² ... 1.5 mm² (TWIN ferrule with plastic sleeve)
Conductor cross-section AWG	30 ... 12
Tightening torque	0.45 Nm ... 0.55 Nm (Usually these terminal blocks must be supported during conductor connection (held by one hand, supported on the housing))

Dimensions

Item dimensions

Width	6.2 mm
Height	80 mm
Depth	94 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54
Ambient temperature (operation)	-25 °C ... 55 °C (Observe derating in the connected state)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	≤ 2000 m (Without derating)
	≤ 3000 m (With correction factor for ambient temperature (operation) x 0.88)
Permissible humidity (operation)	95 %

Approvals

UL, USA/Canada

Identification	UL 2367
	UL 60947-1
	UL 60947-5-1
	CSA C22.2 No. 60947-1
	CSA C22.2 No. 60947-5-1

UL data

Operating mode	Indoor use
----------------	------------

Standards and regulations

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Electromagnetic compatibility (EMC)

Standards/regulations	EN 61000-6-2
	EN 61000-6-3

Air clearances and creepage distances


Standards/regulations	IEC 60664
-----------------------	-----------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any


Drawings

Functional drawing




Setting options

Diagram




Tripping characteristics in FUSE MODE

Diagram



Tripping characteristics in HICCUP MODE

Diagram



Derating

- (1) Individual setup (mounting distance 5 cm) or installed in a row without mounting distance with PLC-R... or PLC-O... (excluding PLC-R...CB...)
- (2) Installed in a row without mounting distance with PLC-R...CB...
- (3) Installed in a row without mounting distance with PLC-R...CB... and PLC-V8...


PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Circuit diagram



Basic circuit diagram

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1328357>



UL Recognized

Approval ID: E317172



cULus Listed

Approval ID: E140324

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Classifications

ECLASS

ECLASS-13.0	27140401
ECLASS-15.0	27140401

ETIM

ETIM 10.0	EC003538
-----------	----------

PLC-RSC- 24DC/1/CB1-6 - Relay module



1328357

<https://www.phoenixcontact.com/us/products/1328357>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

EF3.1 Climate Change

CO2e kg	2.953 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com