

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power cable, 5-position, PUR halogen-free, gray RAL 7001, Plug straight M12, coding: L, on Socket straight M12, coding: L, cable length: 12 m, For direct current up to 12 A/63 V

## Your advantages

- Easy and safe: 100 % electrically tested plug-in components
- Protection against mismatching, thanks to special L-coding
- Our standard: robust halogen-free PUR cable

## Commercial data

Item number	1276472
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF05
Product key	AF1CDP
GTIN	4063151470395
Weight per piece (including packing)	1,521.8 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	PL

1276472

<https://www.phoenixcontact.com/us/products/1276472>

## Technical data

### Product properties

Product type	Power cable
Application	Energy supply
Number of positions	5
Shielded	no
Coding	L

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	V0
--	----

### Electrical properties

Nominal voltage $U_N$	63 V DC
Nominal current $I_N$	12 A

### Connector

#### Connection 1

Type	Plug straight M12
Coding type	L (Power)

#### Connection 2

Type	Socket straight M12
Coding type	L (Power)

### Cable/line

Cable length	12 m
--------------	------

#### PUR halogen-free gray [290]

Dimensional drawing	
Cable weight	100 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Shielded	no

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

Cable type	PUR halogen-free gray [290]
Conductor structure, voltage supply	44x 0.20 mm
AWG power supply	16
Conductor cross-section	5x 1.5 mm <sup>2</sup>
Wire diameter incl. insulation	2.2 mm ±0.05 mm
External cable diameter	7.50 mm ±0.25 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black, pink
Thickness, insulation	≥ 0.26 mm
Thickness, outer sheath	approx. 0.70 mm
Max. conductor resistance	≤ 14.1 Ω/km (at 20 °C)
Insulation resistance	≥ 1 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V AC
Test voltage	≥ 3000 V AC (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	38 mm
Smallest bending radius, movable installation	75 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s <sup>2</sup>
Dynamic load capacity (torsion)	Torsion: ±180 °/m, Torsion cycles: 500000, Torsional frequency: 35 cycles/min.
Halogen-free	in accordance with DIN VDE 0472 part 815 according to IEC 60754-1
Flame resistance	in accordance with UL 758/1581 FT2 complying with IEC 60332-2-2
Resistance to oil	according to DIN EN 60811-404, 168 h at 100 °C
Other resistance	Hydrolysis and microbe resistant as per VDE 0282 section 10 Low adhesion abrasion-resistant Resistant to salt water
Ambient temperature (operation)	-50 °C ... 85 °C (cable, fixed installation) -30 °C ... 85 °C (Cable, flexible installation)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP67

## Standards and regulations

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-111

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

## Drawings



Plug, M12 x 1, straight, shielded



M12 x 1 socket, straight

1276472


<https://www.phoenixcontact.com/us/products/1276472>

Schematic diagram



Pin assignment of M12 connector, 5-pos., L-coded, pin side view

Schematic diagram



Pin assignment of M12 socket, 5-pos., L-coded, socket side view

1276472

<https://www.phoenixcontact.com/us/products/1276472>



Base curve

Circuit diagram



Contact assignment of M12 connector/socket

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1276472>



**UL Listed**

Approval ID: E468743



**cUL Listed**

Approval ID: E468743

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

## Classifications

### ECLASS

ECLASS-13.0	27060327
ECLASS-15.0	27060327

### ETIM

ETIM 10.0	EC001855
-----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# SAC-5P-M12MSL/12,0-290/FSL FE - Power cable



1276472

<https://www.phoenixcontact.com/us/products/1276472>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)