

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Redundancy module STEP DIODE, DIN rail mounting, 5 V DC ... 24 V DC, 1x 10 A, 2x 5 A



## Product description

A safe redundant system is the result of the parallel connection of two power supply units which are decoupled from one another. To further increase system availability, STEP DIODE provides the solution: decoupling with diode.

## Your advantages

- Flexible mounting by simply snapping onto the DIN rail
- Rugged design
- Consistent redundancy up to the load

## Commercial data

Item number	1283937
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM18
Product key	CMRH43
GTIN	4063151488949
Weight per piece (including packing)	78 g
Weight per piece (excluding packing)	54 g
Customs tariff number	85363010
Country of origin	VN

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

## Technical data

### Input data

Nominal input voltage range	5 V DC ... 24 V DC
Input voltage range	4.5 V DC ... 30 V DC
Voltage type of supply voltage	DC
Nominal input current ( $I_N$ )	1x 10 A
	2x 5 A
Reverse polarity protection	yes, < 60 V DC
Voltage drop, input/output	typ. 0.5 V ( $I_{OUT} = 5 A$ )
Transient surge protection	Transil diode

### Output data

Nominal output voltage	$U_{in} - 0,5 V$
Nominal output current ( $I_N$ )	2x 5 A
	1x 10 A
Derating	50 °C ... 70 °C (2 % / K)

### Connection data

#### Conductor connection

Connection method	Push-in connection
rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
flexible with ferrule without plastic sleeve	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	1 mm <sup>2</sup> (recommended)
flexible with ferrule with plastic sleeve	0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>
	1 mm <sup>2</sup> (recommended)
AWG	24 ... 14 (Cu)
Stripping length	10 mm (rigid/flexible/ferrule without plastic sleeve)
	13 mm (Ferrule with plastic sleeve)

#### Conductor connection

Connection method	Push-in connection
rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
flexible with ferrule without plastic sleeve	0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
	1 mm <sup>2</sup> (recommended)
flexible with ferrule with plastic sleeve	0.2 mm <sup>2</sup> ... 1 mm <sup>2</sup>
	1 mm <sup>2</sup> (recommended)
AWG	24 ... 14 (Cu)
Stripping length	10 mm (rigid/flexible/ferrule without plastic sleeve)
	13 mm (Ferrule with plastic sleeve)

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module

1283937

<https://www.phoenixcontact.com/us/products/1283937>

## Electrical properties

Insulation voltage input/output	550 V AC
Insulation voltage input, output / housing	550 V AC

## Product properties

Product type	Redundancy module
Product family	STEP DIODE
MTBF (IEC 61709, SN 29500)	> 29675000 h (25 °C)
	> 18693000 h (40 °C)
	> 13996000 h (50 °C)
LED	yes

## Insulation characteristics


Protection class	III
Degree of pollution	2

## Dimensions

### Item dimensions

Width	18 mm
Height	90 mm
Depth	61 mm
Depth (Device depth (DIN rail mounting))	55 mm (Device depth (DIN rail mounting))

### Dimensional drawing



Horizontal pitch	1 Div. (DIN 43880)
------------------	--------------------

### Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	30 mm / 30 mm

## Mounting

Mounting type	DIN rail mounting
Assembly note	alignable: 0 mm horizontally, 30 mm vertically
Mounting position	horizontal DIN rail NS 35, EN 60715

## Material specifications

Flammability rating according to UL 94 (housing / terminal blocks)	V0
--	----

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

Housing material	Metal
Housing material	PC
Foot latch material	Polyamid

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-10 °C ... 70 °C (Derating: > 50 °C; 2 %/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Maximum altitude	≤ 5000 m (> 2000 m, Derating: 10 %/1000 m)
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Dry heat (IEC 60068-2-2)	70 °C (16 h)
Humid heat cyclic (IEC 60068-2-30)	55 °C (95 %, 2 x 23 h)
Cold (IEC 60068-2-1)	-25 °C (16 h)
Shock (operation)	18 ms, 30g, per spatial direction (IEC 60068-2-27)
Vibration (operation)	< 15 Hz, amplitude ±2.5 mm (IEC 60068-2-6)
	15 Hz ... 150 Hz, 2.3g, 90 min.

## Standards and regulations

### Electrical safety

Standard designation	Electrical safety
Standards/specifications	IEC 61010-1 (SELV)

### Protective extra-low voltage

Standard designation	Protective extra-low voltage
Standards/specifications	IEC 61010-1 (SELV)
	IEC 61010-2-201 (PELV)

## Approvals

### Shipbuilding

Identification	DNV
----------------	-----

### UL

Identification	UL/C-UL Listed UL 61010-1
----------------	---------------------------

### UL

Identification	UL/C-UL Listed UL 61010-2-201
----------------	-------------------------------

### UL

Identification	UL/C-UL Listed ANSI/UL 121201 Class I, Division 2, Groups A, B, C, D (Hazardous Location)
Note	T4 (-10°C ... +70°C, >50°C, derating: 2%/K)

## EMC data

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
Noise immunity	EN 61000-6-2:2019

## Fast transients (burst)

Standards/regulations	EN 61000-4-4
-----------------------	--------------

## Fast transients (burst)

Input	4 kV (Test Level 4 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion B

## Surge voltage load (surge)

Standards/regulations	EN 61000-4-5
-----------------------	--------------

## Surge voltage load (surge)

Input	1 kV (Test Level 3 - symmetrical)
	2 kV (Test Level 3 - asymmetrical)
Output	1 kV (Test Level 3 - symmetrical)
	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion B

## Conducted interference

Input/output/signal	asymmetrical
Frequency range	150 kHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)

## Criteria

Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module




1283937

<https://www.phoenixcontact.com/us/products/1283937>

## Drawings

Dimensional drawing




1283937

<https://www.phoenixcontact.com/us/products/1283937>


Schematic diagram

## Housing



Test sections, insulation voltage

Diagram




# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module

1283937

<https://www.phoenixcontact.com/us/products/1283937>

Block diagram



# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1283937>



**IECEE CB Scheme**  
Approval ID: DK-122039-UL



**EAC**  
Approval ID: RU S-DE.BL08.W.00764



**cULus Listed**  
Approval ID: FILE E 123528

**DNV**

Approval ID: TAA000011F



**cULus Listed**  
Approval ID: FILE E 199827

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

## Classifications

### ECLASS

ECLASS-13.0	27371010
ECLASS-15.0	27371010

### ETIM

ETIM 10.0	EC000683
-----------	----------

### UNSPSC

UNSPSC 21.0	32151500
-------------	----------

# STEP3-DIODE/5-24DC/2X5/1X10/PT - Redundancy module



1283937

<https://www.phoenixcontact.com/us/products/1283937>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	8f786d5d-f2f8-461e-ac91-4f048febfb2

### EF3.1 Climate Change

CO2e kg	2.263 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)